

## Fastening clip - HSCP-CB 4U-7035 - 1056722

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




ME-IO Blockbelt, for 4 PCB connectors, color: light gray (7035)

### Your advantages

- ✔ Enables the functional grouping of various connector plugs
- ✔ Simplifies service and maintenance work
- ✔ Fast mounting and removal of the clamps through a latch system

### Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 055626 697802
GTIN	4055626697802

### Technical data

#### Item properties

Brief article description	Fastening clip
Type	HSCP-CB 4U-7035
Order No.	1056722
Housing type	ME-IO Blockbelt
Type	for 4 PCB connectors
Mounting type	Snap in

#### Material data

Housing material	Polyamide
Color (RAL)	light gray (7035)
Flammability rating according to UL 94	V0

#### Ambient conditions

# Fastening clip - HSCP-CB 4U-7035 - 1056722

## Technical data

### Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
Relative humidity (storage/transport)	80 %

### Packaging information

Pieces per package	50
Denomination packing units	Pcs.

### Standards and regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27182702
eCl@ss 6.0	27180800
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702
eCl@ss 9.0	27182702

### ETIM

ETIM 5.0	EC001031
ETIM 6.0	EC001031
ETIM 7.0	EC001031

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

### Approval details

## Fastening clip - HSCP-CB 4U-7035 - 1056722

### Approvals

EAC



B.01742

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1056722](#)