


Adapter - HC-NPT-3/4-M25 - 1686850

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



NPT adapter, IP68, up to 5 bar, incl. O-ring seal, M25 to 3/4"

Key Commercial Data

Packing unit	25 pc
GTIN	 4 017918 822712
GTIN	4017918822712

Technical data

Dimensions

Length	28 mm
Length without connecting thread	21 mm
Connecting thread diameter	25 mm
Length of the connecting thread	7 mm

Ambient conditions

Degree of protection (IP)	IP68 (Depends on the screw connection used)
Ambient temperature (operation)	-20 °C ... 80 °C

General

Material	Brass, nickel-plated
O-ring material	NBR
Thread type on connection side	M25
Thread type on seal side	3/4 inch NPT
Color	silver

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years

Adapter - HC-NPT-3/4-M25 - 1686850


Technical data

Environmental Product Compliance

	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"
--	---

Drawings

Dimensional drawing



Dimensional drawing

Classifications

eCl@ss

eCl@ss 10.0.1	27430314
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27149100

Adapter - HC-NPT-3/4-M25 - 1686850

Classifications

eCl@ss

eCl@ss 6.0	27149100
eCl@ss 7.0	27439207
eCl@ss 8.0	27439207
eCl@ss 9.0	27430314

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000441
ETIM 5.0	EC000938
ETIM 6.0	EC000938
ETIM 7.0	EC000938

UNSPSC

UNSPSC 6.01	31261502
UNSPSC 7.0901	31261502
UNSPSC 11	31261502
UNSPSC 12.01	31261502
UNSPSC 13.2	31261502

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

EAC		RU C- DE.AI30.B.01102
-----	---	--------------------------

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1686850](#)