


Screw plug - HC-M-BS-M40 - 1645875

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Screw plug, cable gland material: Nickel-plated brass, connecting thread: M40 x 1.5, color: silver



Key Commercial Data

Packing unit	10 pc
GTIN	 4 017918 951122
GTIN	4017918951122

Technical data

Dimensions

Length	12 mm
Length without connecting thread	4 mm
Connecting thread diameter	40 mm
Wrench size, union nut	44 mm
Hexagon angular dimension	50 mm
Length of the connecting thread	8 mm

Ambient conditions

Degree of protection (IP)	IP68
Ambient temperature (operation)	-20 °C ... 80 °C

General

Cable gland material	Nickel-plated brass
O-ring material	NBR
Thread type on connection side	M40 x 1.5
Torque	10 Nm
Color	silver

Standards and Regulations

Screw plug - HC-M-BS-M40 - 1645875

Technical data

Standards and Regulations


Halogen-free	no
--------------	----

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Dimensional drawing



Dimensional drawing

Screw plug - HC-M-BS-M40 - 1645875

Classifications

eCl@ss

eCl@ss 10.0.1	23111190
eCl@ss 4.0	27141200
eCl@ss 4.1	27141200
eCl@ss 5.0	27149100
eCl@ss 5.1	27149100
eCl@ss 6.0	27149100
eCl@ss 7.0	27149110
eCl@ss 8.0	23111190
eCl@ss 9.0	23111190

ETIM

ETIM 2.0	EC000441
ETIM 3.0	EC000441
ETIM 4.0	EC000032
ETIM 5.0	EC000723
ETIM 6.0	EC000451
ETIM 7.0	EC000451

UNSPSC

UNSPSC 6.01	30211808
UNSPSC 7.0901	39121408
UNSPSC 11	39121408
UNSPSC 12.01	39121408
UNSPSC 13.2	31161501
UNSPSC 18.0	31261502
UNSPSC 19.0	31261502
UNSPSC 20.0	31261502
UNSPSC 21.0	31261502

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1645875](#)