

Inline terminal - IB IL 230 PWR IN/F-D-PAC - 2878971

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Inline power terminal, complete with accessories (connector and labeling field), 230 V AC, with fuse and diagnostics

Your advantages

- ✓ Supplying the L phase (230 V AC)
- ✓ L phase protected by an internal fuse
- ✓ Diagnostic and status indicators



Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 083522
GTIN	4046356083522

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	36.6 mm
Height	119.8 mm
Depth	71.5 mm

Interfaces

Connection method	Inline data jumper
Interface	Inline local bus

Power supply

I/O voltage	230 V AC
I/O voltage range	207 V AC ... 253 V AC (including all tolerances, including ripple)

Inline terminal - IB IL 230 PWR IN/F-D-PAC - 2878971

Technical data

Power supply

Max. current consumption	8 A
--------------------------	-----

General


Weight	80 g
--------	------

Inline potentials

Designation	Communications power (U _L)
Supply voltage	7.5 V DC (via voltage jumper)
Current consumption	max. 25 mA
Designation	I/O supply
Supply voltage	230 V AC (via Inline connector)
Supply voltage range	207 V AC ... 253 V AC
Power supply unit	max. 8 A (nominal value)


Drawings

Connection diagram



Inline terminal - IB IL 230 PWR IN/F-D-PAC - 2878971

Dimensional drawing



Classifications

eCl@ss

eCl@ss 10.0.1	27242610
eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27250300
eCl@ss 5.1	27242600
eCl@ss 6.0	27242600
eCl@ss 7.0	27242610
eCl@ss 8.0	27242610
eCl@ss 9.0	27242610

ETIM

ETIM 2.0	EC001433
ETIM 3.0	EC001600
ETIM 4.0	EC001600
ETIM 5.0	EC001600
ETIM 6.0	EC001600
ETIM 7.0	EC001600

UNSPSC

UNSPSC 6.01	43172015
UNSPSC 7.0901	43201404

Inline terminal - IB IL 230 PWR IN/F-D-PAC - 2878971

Classifications

UNSPSC

UNSPSC 11	43172015
UNSPSC 12.01	43201404
UNSPSC 13.2	32151602
UNSPSC 18.0	32151602
UNSPSC 19.0	32151602
UNSPSC 20.0	32151602
UNSPSC 21.0	32151602

Accessories

Accessories

Connector set

Connector set - IB IL AC-PWR-IN-PLSET - 2740180



Connector set, for Inline input terminal blocks with AC voltage

Fuse

Fuse - SI 5X20 6,3 A T DIN 41662 - 2726104



Replacement fuse

Labeling panel

Labeling field - IB IL FIELD 2 - 2727501

Labeling field, width: 12.2 mm



Terminal marking

Inline terminal - IB IL 230 PWR IN/F-D-PAC - 2878971

Accessories

Insert strip - ESL 62X10 - 0809492



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems: Laser printer, mounting type: insert, lettering field size: 62 x 10 mm, Number of individual labels: 72

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2878971](#)