


# Power supply unit - VMT EXT PS - 2900904

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Accessories, external power supply unit for an IPC in IP65 housing



## Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 126892
GTIN	4046356126892

## Technical data

### Power supply unit

Input voltage range AC	96 V AC ... 264 V AC
AC frequency range	47 Hz ... 63 Hz
Output voltage	24 V DC
Output power	72 W

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Classifications

### eCl@ss

eCl@ss 10.0.1	27242209
eCl@ss 4.0	27250300
eCl@ss 4.1	27250300
eCl@ss 5.0	27259200
eCl@ss 5.1	27259200
eCl@ss 6.0	27249200

# Power supply unit - VMT EXT PS - 2900904

## Classifications

### eCl@ss

eCl@ss 7.0	27249290
eCl@ss 8.0	27242209
eCl@ss 9.0	27242209

### ETIM

ETIM 2.0	EC000313
ETIM 3.0	EC000313
ETIM 4.0	EC000599
ETIM 5.0	EC000599
ETIM 6.0	EC000599
ETIM 7.0	EC000599

### UNSPSC

UNSPSC 6.01	30211824
UNSPSC 7.0901	39121421
UNSPSC 11	39121421
UNSPSC 12.01	39121421
UNSPSC 13.2	39121552
UNSPSC 18.0	39121004
UNSPSC 19.0	39121004
UNSPSC 20.0	39121004
UNSPSC 21.0	39121004

## Approvals

### Approvals

---

Approvals


EAC

---

Ex Approvals

---

### Approval details

EAC		RU *- DE.A*30.B.00238
-----	---	--------------------------

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2900904](#)