

Connection element - HV M5/1-VS 2 - 3049437


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Connection element, length: 27 mm, width: 12 mm, height: 4 mm, number of positions: 2, color: silver



Key Commercial Data

| | |
|------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 046356 313544 |
| GTIN | 4046356313544 |

Technical data

Technical data

| | |
|----------------------|--------|
| Color | silver |
| Material | Copper |
| Number of positions | 2 |
| Length | 27 mm |
| Height | 4 mm |
| Width | 12 mm |
| Hole diameter | 5.6 mm |
| Drill hole spacing | 15 mm |
| Maximum load current | 76 A |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Connection element - HV M5/1-VS 2 - 3049437

Classifications

eCl@ss

| | |
|---------------|----------|
| eCl@ss 10.0.1 | 27141190 |
| eCl@ss 4.0 | 27141100 |
| eCl@ss 4.1 | 27141100 |
| eCl@ss 5.0 | 27141100 |
| eCl@ss 5.1 | 27141100 |
| eCl@ss 6.0 | 27141100 |
| eCl@ss 7.0 | 27141190 |
| eCl@ss 8.0 | 27141190 |
| eCl@ss 9.0 | 27141190 |

ETIM

| | |
|----------|----------|
| ETIM 3.0 | EC000483 |
| ETIM 4.0 | EC000483 |
| ETIM 5.0 | EC002848 |
| ETIM 6.0 | EC002848 |
| ETIM 7.0 | EC002848 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211827 |
| UNSPSC 7.0901 | 39121424 |
| UNSPSC 11 | 39121424 |
| UNSPSC 12.01 | 39121424 |
| UNSPSC 13.2 | 39121410 |
| UNSPSC 18.0 | 39121410 |
| UNSPSC 19.0 | 39121410 |
| UNSPSC 20.0 | 39121410 |
| UNSPSC 21.0 | 39121410 |

Approvals

Approvals

Approvals

EAC

Ex Approvals

Approval details

Connection element - HV M5/1-VS 2 - 3049437

Approvals

EAC



RU C-
DE.A*30.B.01742

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3049437](#)