

## Blind rivet - RVT-AL/ST 4,8/14 - 3240553

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




Blind rivets, Ø 4.8 mm, 14 mm sleeve length, aluminum sleeve, zinc-plated steel pin, flat head, standard version similar to DIN 7337 A

### Your advantages

- ✓ Special rivets are available for fixing RW... and UW... high-current panel feed-through terminal blocks that are specifically designed for terminal blocks
- ✓ Compact, ergonomically shaped pliers
- ✓ 3 inserts for rivet diameter of 2.4 - 3.2 mm, 4 mm, and 4.8 - 5.0 mm

### Key Commercial Data

Packing unit	500 pc
GTIN	 4 046356 537940
GTIN	4046356537940

### Technical data

#### Dimensions

Length (b)	14 mm
Hole diameter	4.9 mm
Diameter	4.8 mm
Max. material thickness	10 mm
Material thickness (g)	8 mm

#### General

Color	silver
Material	Aluminum (AlMg 3/3.5)/galvanized steel

## Blind rivet - RVT-AL/ST 4,8/14 - 3240553

### Classifications

#### eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27141137
eCl@ss 5.1	23120400
eCl@ss 6.0	23120400
eCl@ss 7.0	23120402
eCl@ss 8.0	23120402
eCl@ss 9.0	23120402

#### ETIM

ETIM 3.0	EC001675
ETIM 4.0	EC001675
ETIM 5.0	EC002339
ETIM 6.0	EC002339
ETIM 7.0	EC002339

#### UNSPSC

UNSPSC 6.01	30211923
UNSPSC 7.0901	27121703
UNSPSC 11	27121703
UNSPSC 12.01	27121703
UNSPSC 13.2	31162201
UNSPSC 19.0	31162201

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

**PHOENIX CONTACT GmbH & Co. KG**  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240553](#)