

# Cover profile - CD-HF COVER 60 BU - 3240614

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Cover for cable duct, blue, halogen-free, width: 60 mm, length: 2000 mm



## Key Commercial Data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	
GTIN	4046356630306

## Technical data

### Dimensions

Length (b)	2000 mm
Width (a)	60 mm
Height (c)	14.4 mm

### Ambient conditions

Ambient temperature (operation)	-40 °C ... 90 °C
---------------------------------	------------------

### General

Color	blue
Components	halogen-free
Flammability rating according to UL 94	V0
Material	PC/ABS

### Standards and Regulations

Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
------------	---

# Cover profile - CD-HF COVER 60 BU - 3240614

## Technical data

### Environmental Product Compliance

	No hazardous substances above threshold values
--	--

## Classifications

### eCl@ss

eCl@ss 10.0.1	27400776
eCl@ss 4.0	27140600
eCl@ss 4.1	27140600
eCl@ss 5.0	27140600
eCl@ss 5.1	27140600
eCl@ss 6.0	27400700
eCl@ss 7.0	27400776
eCl@ss 8.0	27400776
eCl@ss 9.0	27400776

### ETIM

ETIM 4.0	EC000727
ETIM 5.0	EC000727
ETIM 6.0	EC000727
ETIM 7.0	EC000727

### UNSPSC

UNSPSC 6.01	30101815
UNSPSC 7.0901	30101815
UNSPSC 11	30101815
UNSPSC 12.01	30101815
UNSPSC 13.2	39131712
UNSPSC 18.0	39131712
UNSPSC 19.0	39131712
UNSPSC 20.0	39131712
UNSPSC 21.0	39131712

## Approvals

### Approvals

---

#### Approvals

VDE Zeichengenehmigung

---

#### Ex Approvals

## Cover profile - CD-HF COVER 60 BU - 3240614

### Approvals

---

#### Approval details

VDE Zeichengenehmigung



[http://www2.vde.com/de/Institut/Online-Service/  
VDE-gepruefteProdukte/Seiten/Online-Suche.aspx](http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx)

40028972

---

Phoenix Contact 2020 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240614](#)