

Protective hose - WP-STEEL PVC C 10 - 3240867


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Galvanized steel protective hose with PVC coating



Key Commercial Data

Packing unit	10 M
Minimum order quantity	10 M
GTIN	 4 046356 737227
GTIN	4046356737227

Technical data

Dimensions

Inner diameter (f)	7 mm
Outside diameter	10 mm

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
Short-term temperature	100 °C
Degree of protection	IP68

General

Color	black
Type	Spirals, sheathed
Material	Steel, galvanized/PVC
Bending radius, static	25 mm
Bending radius, dynamic	65 mm
Tensile strength	500 N

Standards and Regulations

Halogen-free	no
--------------	----

Protective hose - WP-STEEL PVC C 10 - 3240867

Classifications

eCl@ss

eCl@ss 10.0.1	27430301
eCl@ss 4.0	27140900
eCl@ss 4.1	27140900
eCl@ss 5.0	27140900
eCl@ss 5.1	27140900
eCl@ss 6.0	27140900
eCl@ss 7.0	27430301
eCl@ss 8.0	27430301
eCl@ss 9.0	27430301

ETIM

ETIM 3.0	EC000897
ETIM 4.0	EC001179
ETIM 5.0	EC001179
ETIM 6.0	EC001179
ETIM 7.0	EC001179

UNSPSC

UNSPSC 6.01	30211812
UNSPSC 7.0901	39121410
UNSPSC 11	39121411
UNSPSC 12.01	39121411
UNSPSC 13.2	40141734
UNSPSC 18.0	40141734
UNSPSC 19.0	40141734
UNSPSC 20.0	40141734
UNSPSC 21.0	40141734

Approvals

Approvals

Approvals

VDE Zeichengenehmigung

Ex Approvals

Approval details

Protective hose - WP-STEEL PVC C 10 - 3240867

Approvals

VDE Zeichengenehmigung



<http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx>

Accessories

Accessories

Corrugated pipe screw connection

Screw connection - WP-G BRASS IP65 PG7 - 3241051



Cable gland made from brass with Pg thread, IP65 protection

Screw connection - WP-G BRASS IP65 M10 - 3241058



Cable gland made from brass with metric thread, IP65 protection

Mounting material

Hose clamp - WP-BASE HF 9-10 - 3240965



Hose clamps

Protective cap

Cable protection end sleeve - WP-SC BRASS WP PVC 10 - 3241072



End sleeves as cable protection, made of brass, for WP-STEEL PVC C

Phoenix Contact 2020 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[3240867](#)