



Main

Range	TeSys
Product or Component Type	Extended rotary handle
Device short name	GV7AP
Range compatibility	TeSys GV7 motor circuit breaker TeSys GV5 motor circuit breaker
Accessory / separate part category	Control accessory
Rotary handle mounting location	Front
Rotary handle mounting style	Extended

Complementary

Handle colour	Red
Handle front plate colour	Yellow
Back/door distance	7.28...23.62 in (185...600 mm)
Rotary handle padlocking	1 to 3 padlocks 0.20...0.31 in (5...8 mm) Padlock in OFF position
Net Weight	1.71 lb(US) (0.775 kg)

Environment

IP Degree of Protection	IP55
-------------------------	------

Ordering and shipping details

Category	22366-MAN STR PROTECTORS-GV1/GV3
Discount Schedule	I11
GTIN	3389110567342
Nbr. of units in pkg.	1
Package weight(Lbs)	25.64 oz (727.0 g)
Returnability	Yes
Country of origin	FR

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.94 in (10.0 cm)
Package 1 width	4.13 in (10.5 cm)
Package 1 Length	19.41 in (49.3 cm)
Unit Type of Package 2	P06
Number of Units in Package 2	12
Package 2 Weight	37.97 lb(US) (17.224 kg)
Package 2 Height	19.69 in (50.0 cm)
Package 2 width	31.50 in (80.0 cm)
Package 2 Length	23.62 in (60.0 cm)
Unit Type of Package 3	S04
Number of Units in Package 3	6
Package 3 Weight	11.57 lb(US) (5.25 kg)

Package 3 Height	11.81 in (30.0 cm)
Package 3 width	15.75 in (40.0 cm)
Package 3 Length	23.62 in (60.0 cm)


Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------

Extended Rotary Handle GV7AP01, GV7AP02



l: 185 minimum, 600 maximum

The shaft of the extended rotary handle GV7AP01 or GV7AP02 must be cut to length: l – 126 mm.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GV7AP02](#)