

Product availability: Non-Stock - Not normally stocked in distribution facility

Price\*: 416.00 USD



### Main

Range of product	Modicon M171/M172
Accessory / separate part category	Measurement accessory
Accessory / separate part type	Probe

### Complementary

Device mounting	Wall mounted
Mounting Support	Mounting box
[Us] rated supply voltage	9...28 V AC 9...40 V DC
Average consumption in mA	35 MA
Output type	RS485 Modbus RTU +/- 3 % RH RS485 Modbus RTU -40...140 °F (-40...60 °C) +/- 1 °C
Product Specific Application	Humidity control
Electrical connection	Screw-clamp terminals
Fixing Mode	2 fixing points
Width	3.94 In (100 mm)
Height	4.80 In (122 mm)
Depth	1.99 In (50.5 mm)
Product Weight	0.31 Lb(US) (0.14 kg)

### Environment

IP degree of protection	IP65
Ambient Air Temperature for Operation	-40...140 °F (-40...60 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Relative humidity	0...100 %
Pollution degree	2
Overvoltage category	I

## Ordering and shipping details

Category	22537 - M171 / M172 HVAC CONTROLLERS
Discount Schedule	PC12
GTIN	3606481390172
Nbr. of units in pkg.	1
Package weight(Lbs)	7.90 Oz (224 g)
Returnability	No
Country of origin	IT

## Packing Units

Unit Type of Package 1	PCE
Package 1 Height	2.56 In (6.5 cm)
Package 1 width	4.53 In (11.5 cm)
Package 1 Length	5.71 In (14.5 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	24
Package 2 Weight	13.99 Lb(US) (6.344 kg)
Package 2 Height	11.81 In (30 cm)
Package 2 width	11.81 In (30 cm)
Package 2 Length	15.75 In (40 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Product Life Status : **Commercialised**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[TM1SHTM4](#)