



Commercial status

This Product is Obsolete : JUL 08, 2021

⚠ This Product is Obsolete

Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	2 x 1.8 Meter Tel cable User manual
--------------------	--

Physical

Cable length	6 Ft (1.83 m)
Color	Beige
Depth	10.51 In (26.7 cm)
Height	2.01 In (5.1 cm)
Product Weight	2.01 Lb(US) (0.91 kg)
Width	4.25 In (10.8 cm)

Input

Maximum Line Current per phase	15 A
Input Frequency	50/60 Hz +/- 5 Hz auto-sensing
Plug standard	NEMA 5-15P
Nominal Input Voltage	120 V

Output

Number of power socket outlets	7
Outlet standard	NEMA 5-15R

Conformance

UL 1449 TVSS Rating	330
Product Certifications	CSA
Standards	UL 497A UL 1283 UL 1363 UL 1449
Equipment protection policy	Lifetime : \$75000

Environmental

Ambient Air Temperature for Operation	32...104 °F (0...40 °C)
Relative Humidity	0...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	5...113 °F (-15...45 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)

Surge Protection and Filtering

EP Joule Rating	1760 J
Data Lines Protected (multi-line only)	1
NM Surge Response Time (ns)	0 ns common mode
Common mode rejection	60 DB
Peak current	13 KA common mode 13 KA normal mode
Surge energy rating	1680 J
Data line protection	RJ11 Modem/Fax/DSL protection (two wire single line)

Ordering and shipping details

GTIN	00731304000181
Package weight(Lbs)	2.40 Lb(US) (1.09 kg)

Packing Units

Package 1 Height	2.09 In (5.3 cm)
Package 1 width	7.24 In (18.4 cm)
Package 1 Length	12.76 In (32.4 cm)
SCC14	10731304000188
Number of Units in Package 2	12
Package 2 Weight	31.2 Lb(US) (14.15 kg)
Number of Units in Package 3	384

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information

Contractual warranty

Warranty	Limited Lifetime
----------	------------------

Product Life Status : **End of commercialisation**

PRO7T may be replaced by any of the following products:



P8T3

APC Home Office SurgeArrest 8 Outlet with Phone (Splitter) Protection, 120V

Qty 1

Substitution date: |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[PRO7T](#)