

# Product data sheet

Specifications



## APC 19" Rack LCD Console

AP5719

### Overview

<b>Presentation</b>	1U rack-mountable keyboard, mouse, and LCD console with US English keyboard layout.
<b>Lead time</b>	Usually in Stock

### Main

<b>Main Input Voltage</b>	100 V 240 V
<b>Number of rack unit</b>	1U

### General

<b>Provided equipment</b>	C13-C14 power cord Documentation CD Firmware upgrade cable Installation guide NEMA 5-15 power cord PS2 KVM cable Rack mounting hardware Single user rack mount kit USB cable USB KVM cable
---------------------------	---

### Physical

<b>Color</b>	Black
<b>Depth</b>	26.18 in (66.5 cm)
<b>Height</b>	1.73 in (4.4 cm)
<b>Maximum Mounting Depth</b>	41.33 in (104.98 cm)
<b>Minimum mounting depth</b>	26.77 in (68 cm)
<b>Net Weight</b>	38.36 lb(US) (17.4 kg)
<b>Width</b>	18.98 in (48.2 cm)

### Input

<b>Input Frequency</b>	50/60 Hz
------------------------	----------

### Conformance

<b>Product Certifications</b>	C-tick CE Industry Canada KCC NOM UL Listed
-------------------------------	--

VCCI Class A  
VDE  
TAA compliance

---

<b>Standards</b>	EN 55022 Class A EN 55024 EN 60950 FCC Part 15 class A IEC 60950
------------------	--

---

## Environmental

---

<b>Ambient air temperature for operation</b>	32...104 °F (0...40 °C)
--	-------------------------

---

## Supported Hardware

---

<b>Display size</b>	19 inch
<b>Trackball Type</b>	PS/2 Touchpad USB mouse
<b>Display Type</b>	LCD display
<b>LCD Power Consumption</b>	19 W
<b>Pixel size</b>	0.26

---

## Ordering and shipping details

---

<b>GTIN</b>	00731304283294
<b>Package weight(Lbs)</b>	46.28 lb(US) (20.99 kg)

---

## Packing Units

---

<b>Package 1 Height</b>	5.98 in (15.2 cm)
<b>Package 1 width</b>	26.50 in (67.3 cm)
<b>Package 1 Length</b>	32.52 in (82.6 cm)

---

## Offer Sustainability

---

<b>Sustainable offer status</b>	Green Premium product
<b>REACH Regulation</b>	<a href="#">REACH Declaration</a>
<b>REACH free of SVHC</b>	Yes
<b>EU RoHS Directive</b>	Compliant <a href="#">EU RoHS Declaration</a>
<b>Lead free</b>	Yes
<b>Mercury free</b>	Yes
<b>RoHS exemption information</b>	<a href="#">Yes</a>
<b>WEEE</b>	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
<b>Take-back</b>	Take-back program available

---

## Contractual warranty

---

<b>Warranty</b>	2 years repair or replace
-----------------	---------------------------

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP5719](#)