



**Commercial status**  
This Product is Obsolete :

⚠ This Product is Obsolete

## Overview

Lead time	Usually in Stock
-----------	------------------

## Main

Nominal Input Voltage	200 V 208 V 230 V
Output voltage	230 V
Plug standard	IEC 60320 C20
Number of rack unit	1U
Provided equipment	Documentation CD Rack Mounting brackets RS-232 configuration cable Warranty card

## Physical

Color	Black
Height	1.73 In (4.4 cm)
Width	17.01 In (43.2 cm)
Depth	9.02 In (22.9 cm)
Net Weight	8.66 Lb(US) (3.93 kg)
Mounting Location	Front Rear
Mounting preference	No preference
Mounting Mode	Rack-mounted

## Input

Input Frequency	47...63 Hz
Max line current	20 A
Input current limits	20 A

## Output

Maximum Total Current Draw per Phase	16 A
Number of power socket outlets	8 IEC 60320 C13 1 IEC 60320 C19
Protection Type	Without circuit breaker

## Conformance

Product certifications	CUL Listed CE UL Listed
Standards	EN 55022 Class A FCC Part 15 class A

## Environmental

Ambient Air Temperature for Operation	23...113 °F (-5...45 °C)
Relative Humidity	5...95 %
Operating altitude	0...10000 ft
Ambient Air Temperature for Storage	-13...149 °F (-25...65 °C)
Storage Relative Humidity	5...95 %
Storage altitude	0...50000 Ft (0.00...15240.00 m)



## Ordering and shipping details

GTIN	00731304255857
Package weight(Lbs)	12.57 Lb(US) (5.7 kg)

## Packing Units

Package 1 Height	4.49 In (11.4 cm)
Package 1 width	23.62 In (60 cm)
Package 1 Length	13.74 In (34.9 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	 <a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Lead free	Yes
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
Take-back	Take-back program available

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Product Life Status : **Post commercialisation**

AP7723 may be replaced by any of the following products:

---



**AP4423**

RACK ATS, 230V, 16A, C20 IN, (8) C13 (1) C19 OUT

Qty 1

Substitution date: |

---



**AP4434**

Rack ATS, 208V, 20A, C20 in, (8) C13 (1) C19 out

Qty 1

Substitution date: | Migration SPD

---

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[AP7723](#)