

Product data sheet

Characteristics

9001SKS11BH11

Selector switch, Harmony 9001SK, plastic, standard handle, black, 30mm, 2 positions, stay put, 3 C/O



Main

| | |
|---------------------------|-----------------|
| Range of Product | Harmony 9001SK |
| Product or Component Type | Selector switch |
| Device short name | 9001SK |

Complementary

| | |
|-------------------------------|------------------|
| Bezel material | Plastic |
| Mounting diameter | 1.18 in (30 mm) |
| Operator position information | 2 positions |
| Contacts type and composition | 3 C/O |
| Device presentation | Complete product |

Environment

| | |
|---------------------------------------|---|
| Protective treatment | TC |
| Ambient Air Temperature for Storage | -40...158 °F (-40...70 °C) |
| Ambient Air Temperature for Operation | -13...158 °F (-25...70 °C) |
| Electrical shock protection class | Class II IEC 61140 |
| IP degree of protection | IP66 IEC 60529 |
| NEMA degree of protection | NEMA 1/2/3/3R/4/4X/6/12/13 |
| Product Certifications | CE CSA LR24590 class 3211 03 UL listed file E42259 CCN NKCR |

Ordering and shipping details

| | |
|-------------------|-------------------|
| Category | 21429-9001 SK,SKY |
| Discount Schedule | CS1 |
| GTIN | 785901966388 |
| Returnability | No |

Packing Units

| | |
|------------------------------|----------------------|
| Unit Type of Package 1 | PCE |
| Number of Units in Package 1 | 1 |
| Package 1 Height | 6.35 in (16.129 cm) |
| Package 1 Width | 2.50 in (6.35 cm) |
| Package 1 Length | 16.13 in (40.968 cm) |
| Package 1 Weight | 3.20 oz (90.719 g) |

Offer Sustainability

| | |
|----------------------------|--|
| Sustainable offer status | Green Premium product |
| California proposition 65 | WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| REACH Regulation | REACH Declaration |
| REACH free of SVHC | Yes |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| China RoHS Regulation | China RoHS Declaration |
| RoHS exemption information | Yes |
| Environmental Disclosure | Product Environmental Profile |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001SKS11BH11](#)