



### Main

Product or Component Type	Communication card
Range Compatibility	Altivar 212
Communication Port Protocol	LonWorks

### Complementary

Electrical connection	Screw terminal NETA, NETB LonWorks transmission/reception data Screw terminal SHLD LonWorks communication shield Screw terminal G/E grounding terminal Spring terminal F programmable logic input Spring terminal R programmable contact input Spring terminal VIB multifunction programmable analog input Spring terminal CC control circuit equipotential Spring terminal P24 power supply output Screw terminal FLA, FLB, FLC multifunction programmable relay output
Input type	Multifunction programmable logic input F < 24 V DC 5 mA sink or source Multifunction programmable contact input R < 24 V DC 5 mA sink or source Multifunction programmable analog input VIB 10 V DC 30 kOhm
Output type	Multifunction programmable relay output FLA, FLB, FLC 250 V AC 1 A 1 Multifunction programmable relay output FLA, FLB, FLC 250 V AC 0.5 A 0.4 Multifunction programmable relay output FLA, FLB, FLC 30 V DC 0.5 A Power supply output P24 24 V DC 50 mA
Electrical Connection	Screw/spring terminal block
Net Weight	0.11 lb(US) (0.05 kg)

### Ordering and shipping details

Category	22159-ATV212 OPTIONS
Discount Schedule	CP4D
GTIN	3606480388590
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.83 in (7.2 cm)
Package 1 Width	6.77 in (17.2 cm)
Package 1 Length	9.13 in (23.2 cm)
Package 1 Weight	8.08 oz (229.0 g)
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Height	11.81 in (30.0 cm)
Package 2 Width	11.81 in (30.0 cm)

Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	4.85 lb(US) (2.199 kg)

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>

## Contractual warranty

Warranty	18 months
----------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[VW3A21212](#)