

ZCKE67

Limit switch head, Limit switches XC Standard, ZCKE, steel roller plunger reinforced



Main

Range of Product	Telemecanique Limit switches XC Standard
Series name	Standard format
Product or Component Type	Limit switch head
Device short name	ZCKE
Head type	Plunger head
Product Compatibility	XCKJ
Associated body	ZCKJ1 ZCKJ2 ZCKJ41H7 ZCKJ9H29 ZCKJ8H29 ZCKJ6H29 ZCKJ5H7 ZCKJD39H7 ZCKJ21H29 ZCKJ21H7 ZCKJ6 ZCKJ7 ZCKJD35H7 ZCKJD35 ZCKJD37 ZCKJ21 ZCKJ5 ZCKJ41 ZCKJ7H7 ZCKJ4H29 ZCKJ7H29 ZCKJ41H29 ZCKJD37H7 ZCKJ11 ZCKJ2H29 ZCKJ8 ZCKJ11H7 ZCKJ2H7 ZCKJ4 ZCKJD31 ZCKJ6H7 ZCKJ1H29 ZCKJ9 ZCKJD35H29 ZCKJ9H7 ZCKJ8H7 ZCKJ5H29 ZCKJ4H7 ZCKJD39 ZCKJD39H29 ZCKJ11H29 ZCKJD31H7 ZCKJD37H29 ZCKJ1H7 ZCKJD31H29
Movement of operating head	Linear
Type of operator	Roller plunger spring return metal reinforced)
Type of approach	Lateral approach, 2 directions

Complementary

Switch actuation	By 30° cam
Positive opening	With
Head material	Metal

Environment

Ambient Air Temperature for Operation	-13...158 °F (-25...70 °C)
Ambient Air Temperature for Storage	-40...158 °F (-40...70 °C)
Environmental characteristic	Standard environment

Ordering and shipping details

Category	22411-LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	3389110645804
Nbr. of units in pkg.	1
Package weight(Lbs)	5.68 oz (161.0 g)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.65 in (4.2 cm)
Package 1 width	1.77 in (4.5 cm)
Package 1 Length	3.43 in (8.7 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	768
Package 2 Weight	307.21 lb(US) (139.348 kg)
Package 2 Height	30.31 in (77 cm)
Package 2 width	23.62 in (60 cm)
Package 2 Length	31.50 in (80 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKE67](#)