




Product availability: Stock - Normally stocked in distribution facility



### Main

Range of product	8501X
Relay type	Control relay
Product or component type	Standard contact cartridge

### Complementary

Rated breaking capacity	6 A at: 120 V AC for: inductive load control circuit per UL 508 3 A at: 240 V AC for: inductive load control circuit per UL 508 1.5 A at: 480 V AC for: inductive load control circuit per UL 508 1.2 A at: 600 V AC for: inductive load control circuit per UL 508 10 A at: <= 600 V AC for: resistive load control circuit per UL 508 1.1 A at: 125 V DC for: inductive load control circuit per UL 508 0.55 A at: 250 V DC for: inductive load control circuit per UL 508 0.2 A at: 301...600 V DC for: inductive load control circuit per UL 508 4 A at: 125 V DC for: resistive load control circuit per UL 508 0.8 A at: 250 V DC for: resistive load control circuit per UL 508
[Icm] rated short-circuit making capacity	60 A at: 120 V AC for: inductive load control circuit per UL 508 30 A at: 240 V AC for: inductive load control circuit per UL 508 15 A at: 480 V AC for: inductive load control circuit per UL 508 12 A at: 600 V AC for: inductive load control circuit per UL 508 10 A at: <= 600 V AC for: resistive load control circuit per UL 508 1.1 A at: 125 V DC for: inductive load control circuit per UL 508 0.55 A at: 250 V DC for: inductive load control circuit per UL 508 0.2 A at: 301...600 V DC for: inductive load control circuit per UL 508 4 A at: 125 V DC for: inductive load control circuit per UL 508 0.8 A at: 250 V DC for: resistive load control circuit per UL 508
Contacts Configuration	1 NO 1 standard contact cartridge


### Environment

Product certifications	CE UL recognized E78403 CCN NKCR2 CSA LR60905 class 3211 02
------------------------	---

### Ordering and shipping details

Category	21159 - 8501 X ACCESSORIES
Discount Schedule	CP2
GTIN	00785901537175
Nbr. of units in pkg.	1
Package weight(Lbs)	0.02
Returnability	Y
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1332 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[8501XC1](#)