



## Main

Range	Square D X Series
Product or Component Type	Switch
Device Application	Control
Device presentation	Mechanism with fixing frame
Aesthetic name	X Series

## Complementary

Actuator	Dolly
Number of modules	1
Number of gangs	1 gang
Switch Function	1-way
Number of poles	1
[Ie] rated operational current AC	15 A
[Ue] rated operational voltage	120 V 277 V
Network type	AC
Network Frequency	60 Hz
Mounting Mode	By screws
Device mounting	Flush
Material	Plastic strap Metal fixing frame
Surface Finish	Matte
Connections - terminals	Phase and neutral 2 screw terminal AWG 14...AWG 12) copper Phase and neutral 2 push-in termination AWG 14), solid copper Earth 1 screw terminal copper
Earth circuit	Self earthing
Market Segment	Residential
Targeted channel	Distributor

## Environment

Standards	UL 20
Product Certifications	cULus

## Ordering and shipping details

Category	09932-WD BASIC DEVICES
Discount Schedule	DE9
GTIN	785901534563
Returnability	Yes
Country of origin	CN

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.17 in (10.6 cm)
Package 1 Width	1.50 in (3.8 cm)
Package 1 Length	1.77 in (4.5 cm)
Package 1 Weight	2.57 oz (73 g)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Height	4.45 in (11.3 cm)
Package 2 Width	3.82 in (9.7 cm)
Package 2 Length	7.87 in (20 cm)
Package 2 Weight	28.25 oz (801 g)
Unit Type of Package 3	CAR
Number of Units in Package 3	100
Package 3 Height	8.66 in (22 cm)
Package 3 Width	9.49 in (24.1 cm)
Package 3 Length	20.08 in (51 cm)
Package 3 Weight	19.14 lb(US) (8.68 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: carbon black, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	2 years
----------	---------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SQR14101XX](#)