



Main

Product or Component Type	Communication card
Range Compatibility	Altivar 71 Altivar 61Q Altivar 61 Altivar 71Q
Communication Port Protocol	Profibus DP
Connector Type	9-way female SUB-D connector
Transmission Rate	1.5 Mbps 12 Mbps 9600 bps 3 Mbps 500 kbps 19.2 kbps 187.5 kbps 6 Mbps 93.75 kbps

Complementary

Number of addresses	1...126
Communication service	CiA 402 profile I/O profile I/O data Communication monitoring can be inhibited, adjustable PPO type 5
Display type	1 LED DX (data exchange) 1 LED ST (status) Graphic display terminal control word received Graphic display terminal I/O data Graphic display terminal reference received
Net Weight	0.66 lb(US) (0.3 kg)

Ordering and shipping details

Category	22135-ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	3389118067165
Returnability	No
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.83 in (7.200 cm)
Package 1 Width	6.69 in (17.000 cm)
Package 1 Length	9.06 in (23.000 cm)
Package 1 Weight	10.16 oz (288.000 g)
Unit Type of Package 2	S03
Number of Units in Package 2	7
Package 2 Height	11.81 in (30.000 cm)
Package 2 Width	11.81 in (30.000 cm)
Package 2 Length	15.75 in (40.000 cm)
Package 2 Weight	5.54 lb(US) (2.512 kg)

Unit Type of Package 3	P06
Number of Units in Package 3	56
Package 3 Height	29.53 in (75.000 cm)
Package 3 Width	23.62 in (60.000 cm)
Package 3 Length	31.50 in (80.000 cm)
Package 3 Weight	66.99 lb(US) (30.388 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[VW3A3307](#)