



Product availability: Stock - Normally stocked in distribution facility



### Main

Range	TeSys
Device short name	GVAU
Product or component type	Undervoltage trip

### Complementary

Product compatibility	GV2P GV3L GV2ME GV2LE GV3P GV2L
[Uc] control circuit voltage	200 V AC 50 Hz 200...220 V AC 60 Hz
Control circuit voltage limits	0.85...1.1 Un
[Ui] rated insulation voltage	600 V AC CSA C22.2 No 14 600 V AC UL 508 690 V AC IEC 60947-1
Threshold tripping voltage	0.7...0.35 Un
Inrush power in VA	12 VA AC
Inrush power in W	8 W DC
Hold-in power consumption in VA	3.5 VA AC
Hold-in power consumption in W	1.1 W DC
Operating time	10...15 ms IEC 60947-1
On-load factor	100 %
Connections - terminals	Screw clamp terminals 1 0.75...2.5 mm <sup>2</sup> flexible without cable end Screw clamp terminals 2 0.75...2.5 mm <sup>2</sup> flexible without cable end Screw clamp terminals 1 0.75...1.5 mm <sup>2</sup> flexible with cable end Screw clamp terminals 2 0.75...1.5 mm <sup>2</sup> flexible with cable end Screw clamp terminals 1 0...0 in <sup>2</sup> (1...2.5 mm <sup>2</sup> ) solid Screw clamp terminals 2 0...0 in <sup>2</sup> (1...2.5 mm <sup>2</sup> ) solid
Tightening torque	< 1.4 N.m screw clamp terminals
Mechanical durability	10000 cycles with GV3P and GV3L 30000 cycles with GV2ME and GV2P
Quantity per set	Set of 10
Product weight	0.23 lb(US) (0.105 kg)

### Ordering and shipping details

Category	22367 - MANUAL STR PROTECTOR - GV2
Discount Schedule	I11
GTIN	00785901468813
Nbr. of units in pkg.	1
Package weight(Lbs)	0.2600000000000001

Returnability	Y
Country of origin	CZ

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0701 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>


### Contractual warranty

Warranty period	18 months
-----------------	-----------

---

---

GVAU...



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[GVAU207](#)