

# 9001BW245

## CONTROL STATION 600VAC 5A T-B Ø30

### Standard Duty Momentary Pushbuttons

### 1NO-1NC



Product availability: Non-Stock - Not normally stocked in distribution facility



#### Main

Range of product	Harmony 9001BW
Product or component type	Complete control station
Device short name	9001BW
Control station application	Two functions
Colour of base of enclosure	Grey

#### Complementary

Material	Cast aluminium
Cable entry	1 entry for 1/2" - 14 NPT
CAD overall width	2.76 in (70 mm)
CAD overall height	4.25 in (108 mm)
CAD overall depth	3.58 in (91 mm)
Type of operator	Momentary
Control station composition	1 flush push-button, cap/operator or lens colour:black (ON marking) white 1 flush push-button, cap/operator or lens colour:red (OFF marking) white
Contacts type and composition	1 NO + 1 NC
Mechanical durability	5000000 cycles
Connections - terminals	Screw-clamp terminal
[Ie] rated operational current	0.6 A at 600 V - utilisation category AC-1/DC-1 0.75 A at 480 V - utilisation category AC 1.5 A at 240 V - utilisation category AC 3.75 A at 120 V - utilisation category AC
Device mounting	Surface
Type of installation	Indoor/outdoor

#### Environment

Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
NEMA degree of protection	NEMA 1 NEMA 4
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/IEC 60947-5-5 JIS C 4520 UL 508 CSA C22.2 No 14
Product certifications	CSA UL listed
Environmental characteristic	Waterproof Dustproof

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Ordering and shipping details

Category	21421 - 9001 B (NOT BW70 - BW80)
Discount Schedule	CS1
GTIN	00785901857693
Nbr. of units in pkg.	1
Package weight(Lbs)	1.97
Returnability	N
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

## Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001BW245](#)