

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Harmony 9001KY
Product or component type	Control station
Device short name	9001KY
Provided equipment	Label plate with START-STOP marking
Electrical circuit type	Motor
Contact block name	KA1
Product specific application	For hoisting and mechanical handling applications
Level or class	Class III Class II Division 2 Group G

Complementary

Enclosure/cubicle description	Wall-mounted enclosure with 2 cut-outs : Ø 30 mm
Enclosure material	Die cast zinc alloy, colour : grey
Type of installation	Indoor/outdoor
Control station composition	1 pushbutton with 2 NO + 2 NC contacts 1 mushroom button
Mechanical interlocking	Without mechanical interlock
Connector type	Screw clamp connector
Connections - terminals	Direct connection (AWG 2), cable stiffness : solid stranded Direct connection (AWG 12), cable stiffness : solid stranded Direct connection (AWG 24), cable stiffness : solid stranded
[Ue] rated operational voltage	300 V
[Ie] rated operational current AC	10 A


Environment

NEMA degree of protection	NEMA 1 NEMA 13 NEMA 3 NEMA 4
Environmental characteristic	Resistant against immersion in water Dust and oil resistant
Product certifications	UL listed
Ambient air temperature for operation	-13...140 °F (-25...60 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)

Ordering and shipping details

Category	21426 - 9001 K (NOT KA,KM,KX)
Discount Schedule	CS1
GTIN	00785901513407
Nbr. of units in pkg.	1
Package weight(Lbs)	3.3500000000000001
Returnability	N
Country of origin	MX

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1002 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Nickel compounds, which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[9001KYK22](#)