

Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	Harmony XVR
Product or component type	Prewired rotating mirror beacon
Sound signalling	Without
Device short name	XVR
Mounting diameter	3.31 in (84 mm)
IP degree of protection	IP23 conforming to IEC 60529 IP65 (with accessory) conforming to IEC 60529
[Us] rated supply voltage	24 V AC/DC
Light source	High luminosity LED, red

Complementary

Material	ABS (acrylonitrile butadiene-styrene) (body part) PC (globe)
CAD overall width	3.31 in (84 mm)
CAD overall depth	3.31 in (84 mm)
Product weight	0.66 lb(US) (0.3 kg)
Marking	CE
Product mounting	By 3 M4 screws
Supply voltage limits	21.6...26.4 V AC 19...30 V DC
[Uimp] rated impulse withstand voltage	0.8 kV
Current consumption	125 mA
Flashing frequency	2.3 Hz
Clamping connection capacity	0.83 mm ²
AWG gauge	AWG 18
Cable length	19.69 in (500 mm)


Environment

Standards	EN 61000-6-4 EN 61000-6-2
Product certifications	UL
Protective treatment	TC
Ambient air temperature for storage	-31...158 °F (-35...70 °C)
Ambient air temperature for operation	14...122 °F (-10...50 °C)
Electrical shock protection class	Class II conforming to IEC 61140

Ordering and shipping details

Category	22617 - XVC TOWER LIGHTS
Discount Schedule	XV
GTIN	00785901964544
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8599999999999999
Returnability	Y
Country of origin	ID

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1611 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov



Contractual warranty

Warranty period	18 months
-----------------	-----------

Rotating Mirror Beacon


Dimensions

mm
in.



Rotating Mirror Beacon

Panel Cut-out



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XVR08B04](#)