

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCKE
Head type	Multi-directional head
Product compatibility	XCKJ
Associated body	ZCKJ21H7 ZCKJD31 ZCKJ7 ZCKJ7H29 ZCKJD37H7 ZCKJ11H29 ZCKJ2 ZCKJD39H29 ZCKJ8 ZCKJD39H7 ZCKJ1 ZCKJ1H29 ZCKJD37 ZCKJD35H7 ZCKJ7H7 ZCKJ2H7 ZCKJ11H7 ZCKJD39 ZCKJ5H7 ZCKJ6 ZCKJ6H29 ZCKJ9H29 ZCKJ9H7 ZCKJD31H7 ZCKJ21H29 ZCKJ2H29 ZCKJ9 ZCKJD35 ZCKJ8H29 ZCKJD35H29 ZCKJD31H29 ZCKJ1H7 ZCKJD37H29 ZCKJ11 ZCKJ6H7 ZCKJ21 ZCKJ5 ZCKJ5H29 ZCKJ8H7
Movement of operating head	Multi-directional
Type of operator	Spring rod spring return
Type of approach	Multi-directional approach

Complementary

Switch actuation	By any moving part
Positive opening	Without
Product weight	0.28 lb(US) (0.125 kg)
Head material	Metal

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.


Environment

Ambient air temperature for operation	50...248 °F (10...120 °C)
Ambient air temperature for storage	50...248 °F (10...120 °C)
Environmental characteristic	High temperature

Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T
GTIN	003389110599411
Nbr. of units in pkg.	1
Package weight(Lbs)	0.8000000000000004
Returnability	N
Country of origin	FR

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1022 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
----- Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[ZCKE085](#)