



VMP
MID SIZE VIDEO PLUG

UHD
ULTRA HIGH DEFINITION

CABLE LENGTH

CABLE JACKET COLOR

- 1 - 1 FEET ± 1 INCH
- 2 - 2 FEET ± 1 INCH
- 3 - 3 FEET ± 1 INCH
- 4 - 4 FEET ± 1 INCH
- 5 - 5 FEET ± 1 INCH
- 6 - 6 FEET ± 2 INCH
- 7 - 7 FEET ± 2 INCH
- 8 - 8 FEET ± 2 INCH
- 9 - 9 FEET ± 2 INCH
- 10 - 10 FEET ± 2 INCH

- BK** - BLACK
- R** - RED
- O** - ORANGE
- GN** - GREEN
- BL** - BLUE
- P** - PURPLE

0E

CUSTOMER DRAWING

NOTES:

- CABLE: BELDEN 1505A, 4505R, OR ENGINEERING APPROVED EQUIVALENT VIDEO CABLE, 75 OHM MATTE PVC JACKET - SEE CHART FOR COLOR
- PLUG: VIDEO UHD PLUG, MID SIZE, BRASS, NICKEL PLATED
- BOOT: PLASTIC UL94-V0, GRAY COLOR ON ALL CABLES.
- THIS PRODUCT IS RoHS COMPLIANT.

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES

- TWO PLACE DECIMALS ± 0.02
- THREE PLACE DECIMALS ± 0.005

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE	WIDTH	MULT	LBS/M	TEMPER
FINISH			MATERIAL	
SPEC No.			SPEC No.	
FIRST USED ON		SCALE		
DATE DRAWN	BY	CHKD	APVD	
8-9-16	SRC	8-9-16 SRC	8-24-17 SRC	
NAME				SHEET 1 OF 1
MID SIZE VIDEO PLUG PATCH CORD, RoHS				REV 0E
PART No.				VMP1__UHD - VMP10__UHD

REV	ECO NUMBER	DATE	BY	APVD
0E	REMOVED YELLOW GRAY & WHITE	8-24-17	SRC	SRC
0D	ADDED N TO G ADDED GRAY	4-19-17	SRC	SRC
0C	GRAY WAS GREY	3-28-17	SRC	SRC
0B	CHG NUMBER	11-8-16	SRC	SRC
REVISIONS				

SolidWorks CAD File



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[VMP3RUHD](#) [VMP2BKUHD](#) [VMP2GNUHD](#) [VMP3BKUHD](#) [VMP5BKUHD](#) [VMP2RUHD](#)