



- NOTES:
- ALL DIMENSIONS ARE REFERENCE.
 - MATERIALS:
 - HOUSING & COVER: ABS, UL-94VO, BLACK
 - COLOR INSERT: ABS, UL-94HB
 - P.C. BOARD: UL-94VO
 - SHELL & SLEEVE TERMINALS: COPPER ALLOY, NICKEL OR GOLD PLATED
 - TIP & S-VIDEO TERMINALS: COPPER ALLOY, TIN PLATED
 - THIS PART IS RoHS COMPLIANT

PART NUMBER	INSERT (A) COLOR	INSERT (B) COLOR	INSERT (C) COLOR	SHELL AND SLEEVE TERMINAL FINISH
PJRS1X3U01X	YELLOW	WHITE	RED	NICKEL PLATED
PJRS1X3U01AUX	YELLOW	WHITE	RED	GOLD PLATED

CUSTOMER DRAWING

★ STAR SYMBOL DENOTES CRITICAL DIMENSION UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R. 2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002 3. REMOVE ALL BURRS DO NOT SCALE DRAWING					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
FINISH			MATERIAL						
SPEC No.			SPEC No.						
FIRST USED ON		SCALE			SHEET OF				
DATE DRAWN		5:4							
BY	CHKD	APVD							
13-Jan-06	JL	TJK	TJK						
		1-13-06	1-13-06						
NAME					PART No.				
PHONO JACK - RA 3 POS.					PJRS1X3U01X				
VERT. UNSHIELDED W/S-VIDEO, RoHS					PJRS1X3U01AUX				
					REV				
					A				

REV	ECO NUMBER	DATE	BY	APVD
A	25181	1-13-06	JL	TJK

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[PJRAS1X3U01X](#) [PJRAS1X3U01AU](#)