

## 4-Port USB-C Hub, USB-C to 4x USB-A Ports, USB 3.0, Black

MODEL NUMBER: U460-004-4AB



USB 3.1 Type-C hub adds 4 USB-A ports to your laptop, MacBook, Chromebook or other compatible device.

### Features

**USB 3.1 Type-C Hub Connects to Your Device's USB-C or Thunderbolt 3 Port** This USB-C hub expands the potential of your tablet, laptop, Chromebook, MacBook, smartphone or PC's USB-C or Thunderbolt 3 port. It's ideal for adding a thumb drive, external hard drive, digital camera, MP3 player and other USB peripherals.

**Connects Up to 4 USB-A Peripherals** Four USB-A ports accept USB peripherals, such as a flash drive, mouse, keyboard or printer, and all four provide up to 1.5A for charging smartphones and other mobile devices. All ports support fast USB 3.1 Gen 1 data transfer rates up to 5 Gbps and are backward compatible with previous USB generations, so you can continue using older peripherals while getting high-speed performance from new devices. **Note:** Host must support USB OTG (On-the-Go) **Built-In USB-C Cable Connects in Either Direction**

Connect the reversible USB-C plug to your source device's Thunderbolt 3 or USB Type-C connector. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

**Ready to Use Right Out of the Package** The plug-and-play USB 3.1 Type-C hub requires no software, drivers or external power. The lightweight case fits easily into a pocket, briefcase or laptop bag for connecting on the go.

**3-Year Warranty and Environmentally Responsible Design** The U460-004-4AB comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting Tripp Lite's commitment to environmental responsibility.

### Highlights

- Supports USB 3.1 Gen 1 for fast data transfers up to 5 Gbps
- Accepts up to 4 USB peripherals, turning your laptop into a mini workstation
- Reversible USB-C plug connects in either direction for immediate no-fuss use
- USB ports provide up to 5V/1.5A (7.5W) for charging smartphones and other devices
- Easy installation with plug-and-play operation—no software required

### Applications

- Transfer files to and from a USB thumb drive or external hard drive
- Connect your smartphone or other mobile device to build up a full charge
- Attach a USB headset/microphone for recording your podcast
- Write a report using a USB keyboard with your tablet or Android smartphone

### System Requirements

Tablet, laptop, Chromebook, MacBook, smartphone or PC with USB-C or Thunderbolt 3 port.

### Package Includes

U460-004-4AB 4-Port USB 3.1 Hub, 4x USB-A, Thunderbolt - Black

## Specifications



<b>OVERVIEW</b>	
UPC Code	037332209580
Product Type	Hub
Technology	USB 3.0 (SuperSpeed); USB 3.1 (Gen 1); USB
Host Connector	USB C (MALE)
<b>VIDEO</b>	
Number of Monitors Supported	0
Extended Mode	No
Mirror Mode	No
<b>DATA</b>	
Data Ports	(4) USB A (FEMALE)
Data Ports Detail	(4) USB-A - USB 3.2 Gen 1 (5 Gbps)
<b>INPUT</b>	
Bus Powered	Yes
Product Length (in.)	11.7
Product Length (cm.)	29.72
Product Length (ft.)	0.98
Product Length (m.)	0.3
<b>BATTERY</b>	
Battery Charging (5V/1.5A Port)	Yes
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
LED Indicators	White - Power
<b>CHARGING</b>	
Charging Ports / Amps	(4) 1.5A
Charging Ports	USB-A: 5V 1.5A (7.5W)
Total Charging Watts	7.5
<b>PHYSICAL</b>	
Color	Black
Cable Jacket Rating	VW-1
Material of Construction	Plastic



Shipping Dimensions (hwd / in.)	1.06 x 3.00 x 5.70
Shipping Weight (lbs.)	0.20
Unit Dimensions (hwd / cm)	2.14 x 9.65 x 3.05
Unit Dimensions (hwd / in.)	0.84 x 3.8 x 1.2
Unit Packaging Type	Box
Unit Weight (kg)	0.04
Unit Weight (lbs.)	0.09
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32 to 113 F (0 to 45 C)
Storage Temperature Range	14 to 158 F (-10 to 70 C)
Relative Humidity	20% to 80% RH, Non-Condensing
BTUs	2.4 BTU/Hr
Power Consumption (Watts)	0.7
Power Provided to Connected Device(s)	Up to 5V 1.5A (7.5W) per USB Port
<b>CONNECTIONS</b>	
Ports	4
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	(4) USB 3.0 A (FEMALE)
Connector Plating	Nickel
<b>FEATURES &amp; SPECIFICATIONS</b>	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)
Driver Required	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	CE, FCC, RoHS, REACH
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	3-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[U460-004-4AB](#)