


SPECIFICATION

Part No.	: TI.16.5F11
Product Name	: 915MHz 5dBi Outdoors Omni-Directional Rigid Whip Antenna
Feature	: Stable performance at 902 MHz to 928MHz Omni-directional pattern in the azimuth Robust Weatherproof Brass Whip and Casing High Efficiency N-type Male Connector RoHS compliant



I. Introduction


TI.16 is a 5dBi 915MHz ISM band (902MHz to 928MHz) Dipole Omni-directional antenna. This robust whip is suitable for outdoors applications where wide coverage is required especially in the azimuth plane, including metering, remote monitoring. As standard low frequency monopole antenna, its radiation property improves with mounting on metal plate. Connector can be customized on request.

II. Specification Table


ISM 915MHz				
Frequency (MHz)		900	915	925
Peak Gain (dBi)	Free Space	-2.3	-1.7	-1.27
	Ground (30x30cm)	-1.1	-0.3	0.2
	Ground (50x50cm)	3.9	4.6	4.9
Average Gain (dBi)	Free Space	-7.2	-6.8	-6.4
	Ground (30x30cm)	-6.0	-5.2	-4.6
	Ground (50x50cm)	-3.1	-2.2	-1.7
Efficiency	Free Space	19%	21%	22%
	Ground (30x30cm)	25%	30%	35%
	Ground (50x50cm)	49%	60%	68%
Impedance		50Ω		
Polarization		Linear		
Radiation Pattern		Omni		
Input Power		50 W		
MECHANICAL				
Dimensions		620mm		
Base Diameter		25mm		
Whip Diameter		19mm at widest		
Whip Material		Coated Brass		
Connector		N Male Straight		
ENVIRONMENTAL				
Temperature Range		-40°C to 85°C		
Humidity		Non-condensing 65°C 95% RH		

III. Antenna Characteristics


III.1. Return Loss




III.2. Antenna Efficiency



III.3. Peak Gain




III.4. Average Gain




IV. Radiation Patterns


IV.1. Antenna setup (Free Space)




Radiation Pattern

XY plane






IV.2. Antenna setup (with 300x300mm ground plane)




Radiation Pattern


XY plane



XZ plane




IV.3. Antenna setup (with 500x500mm ground plane)




Radiation Pattern


XY plane




XZ plane



V. Drawing



VI. Packaging



1PCS/BAG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taoglas:](#)

[TI.16.5F11](#)