



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
	A	WR-08-38		13AUG2008	KW	CC	

POSITION 1 IDENTIFICATION FEATURE


1 MATERIAL: HOUSING: NYLON, UL94V-0, RED
 CONTACTS: BRASS, TIN-PLATED



24	46.2±0.25 [1.82±.01]	51.6 [2.03]	2-2029136-4
22	42.0±0.25 [1.65±.01]	47.4 [1.87]	2-2029136-2
20	37.8±0.25 [1.49±.01]	43.2 [1.70]	2-2029136-0
18	33.6±0.25 [1.32±.01]	39.0 [1.54]	1-2029136-8
16	29.4±0.25 [1.16±.01]	34.8 [1.37]	1-2029136-6
14	25.2±0.25 [.99±.01]	30.6 [1.21]	1-2029136-4
12	21.0±0.25 [.83±.01]	26.4 [1.04]	1-2029136-2
10	16.8±0.13 [.66±.005]	22.2 [.87]	1-2029136-0
8	12.6±0.13 [.50±.005]	18.0 [.71]	2029136-8
6	8.4±0.13 [.33±.005]	13.8 [.54]	2029136-6
4	4.2±0.13 [.17±.005]	9.6 [.38]	2029136-4
2	-	5.4 [.21]	2029136-2
POS	A	B±0.25[.01]	PART NUMBER



2-2029136-4 SHOWN



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ± 0.13 [.005] 2 PLC ± 0.25 [.01] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH ±	DWN K. WHITAKER 13AUG2008	CHK C. CASH 13AUG2008	APVD C. CASH 13AUG2008	NAME Tyco Electronics Corporation Harrisburg, PA 17105-3608
MATERIAL 1	APPLICATION SPEC	VERTICAL HEADER, RED, WITHOUT PEGS, WITH DRAIN HOLES, VAL-U-LOK(TM)			RESTRICTED TO -
CUSTOMER DRAWING		SCALE 10:1	SHEET 1 of 1	REV A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2029136-2](#)