



Nanonics Standard Catalog Part Number Cross-Reference

Revision 1

TE P/N	TE CD	Nanonics P/N	Part Description
1589691-1	1589691	QCM007PC2DC012B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, backshell.
1589691-2	1589691	QCM007PC2DC018B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 18 inches, backshell.
1589691-3	1589691	QCM007PC2DC036B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 36 inches, backshell.
1589691-4	1589691	QCM007PC2DX006B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, white PTFE wire, 6 inches, backshell.
1589691-5	1589691	QCM007PC2DC006B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches, backshell.
1589691-6	1589691	QCM007PC2DCC20B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 centimeters, backshell.
1589691-7	1589691	QCM007PC2DMC150B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 150 centimeters, backshell.
1589691-8	1589691	QCM007PC2DMC50B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 50 centimeters, backshell.
1589691-9	1589691	QCM007PC2DC020B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 inches, backshell.
1-1589691-0	1589691	QCM007PC2DCC50B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 50 centimeters, backshell.
1-1589691-1	1589691	QCM007PC2DC024B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches, backshell.
1-1589691-2	1589691	QCM007PC2DY036B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, white PTFE wire, 36 inches, backshell.
1-1589691-3	1589691	QCM007PC2DC200B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 200 inches, backshell.
1-1589691-4	1589691	QCM007PC2DC102B	Quick disconnect, circular, metal, 7 position, plug, 30 AWG 7 strand, color coded PTFE wire, 102 inches, backshell.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[QCM007PC2DCC50B](#)