



Nanonics Standard Catalog Part Number Cross-Reference

Revision 1

TE P/N	TE CD	Nanonics P/N	Part Description
1589692-1	1589692	QCM019PC0DM072B	Quick disconnect, circular, metal, 19 position, plug, 28 AWG SOLID, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 72 inches, backshell.
1589692-2	1589692	QCM019PC2DC120B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 120 inches, backshell.
1589692-3	1589692	QCM019PC2DC006B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches, backshell.
1589692-4	1589692	QCM019PC2DMC150B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 150 centimeters, backshell.
1589692-5	1589692	QCM019PC2DC020B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 inches, backshell.
1589692-6	1589692	QCM019PC2DC024B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches, backshell.
1589692-7	1589692	QCM019PC2DC072B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 72 inches, backshell.
1589692-8	1589692	QCM019PC2DMM02B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 2 meters, backshell.
1589692-9	1589692	QCM019PC2DC016B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 16 inches, backshell.
1-1589692-0	1589692	QCM019PC2DM120B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 120 inches, backshell.
1-1589692-1	1589692	QCM019PC2DC012B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches, backshell.
1-1589692-2	1589692	QCM019PC2DM036B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 36 inches, backshell.
1-1589692-3	1589692	QCM019PC2DC048B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 48 inches, backshell.
1-1589692-4	1589692	QCM019PC2DC018B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 18 inches, backshell.
1-1589692-5	1589692	QCM019PC2DC180B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 180 inches, backshell.
1-1589692-6	1589692	QCM019PC0DC042B	Quick disconnect, circular, metal, 19 position, plug, 28 AWG solid, color coded PTFE wire, 42 inches, backshell.
1-1589692-7	1589692	QCM019PC2DC060B	Quick disconnect, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 60 inches, backshell.
1-1589692-8	1589692	QCM019PC3DMC150B	Quick disconnect, circular, metal, 19 position, plug, 32 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 150 centimeters, backshell.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[QCM019PC2DC180B](#)