



LOC		DIST		REVISIONS			
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		K2		REVISED PER ECO-11-004917	11MAR11	RK	HMR



11	OBSOLETE	10	2	2.40	1.198	1-104257-1	12	-6-103961-4
11	OBSOLETE	10	2	2.20	1.098	1-104257-0	11	-6-103961-0
		10	2	2.00	.998	104257-9	10	5-103961-9
		10	2	1.80	.898	104257-8	9	5-103961-8
		10	2	1.60	.798	104257-7	8	5-103961-7
		10	2	1.40	.698	104257-6	7	5-103961-6
		10	4	2.39	.598	104257-5	6	5-103961-5
		10	4	1.99	.498	104257-4	5	5-103961-4
		10	5	1.99	.398	104257-3	4	5-103961-3
		10	8	2.40	.298	104257-2	3	5-103961-2
		10	10	2.00	.198	104257-1	2	5-103961-1
11	OBSOLETE	9	2	2.40	1.198	1-104257-1	12	-1-103961-4
11	OBSOLETE	9	2	2.20	1.098	1-104257-0	11	-1-103961-0
		9	2	2.00	.998	104257-9	10	103961-9
		9	2	1.80	.898	104257-8	9	103961-8
		9	2	1.60	.798	104257-7	8	103961-7
		9	2	1.40	.698	104257-6	7	103961-6
		9	4	2.39	.598	104257-5	6	103961-5
		9	4	1.99	.498	104257-4	5	103961-4
		9	5	1.99	.398	104257-3	4	103961-3
		9	8	2.40	.298	104257-2	3	103961-2
		9	10	2.00	.198	104257-1	2	103961-1
		6		B	A	HOUSING PART NUMBER	NO OF POSN	ASSEMBLY PART NUMBER ON STRIP



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN L A MAYER 11-4-86  
 CHK P de Jong 11-12-86  
 APVD J SCHIEFFER 11-13-86

TE Connectivity

RCPT ASSY, AMPMODU MTE, SINGLE ROW, .100 C/L ROW, .100, LATCHED & POLARIZED, FOR #26-#30 AWG WIRE SIZE, STRIP FORM

108-25034  
 114-25026

SIZE A2 CAGE CODE 00779 DRAWING NO C=103961

SCALE 4:1 SHEET 1 of 1 REV K2

DIMENSIONS: INCHES  
 TOLERANCES UNLESS OTHERWISE SPECIFIED:  
 0 PLC ± -  
 1 PLC ± -  
 2 PLC ± .02  
 3 PLC ± .005  
 4 PLC ± -  
 ANGLES ± -  
 FINISH SEE TABLE

MATERIAL: HOUSING: FLAME RETARDANT THERMOPLASTIC, COLOR-BLACK  
 CONTACTS: PHOS BRONZE

CUSTOMER DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103961-7](#)