


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	V1	REVISED PER ECO-15-002073	06MAY2015	NK	MZ
	W	REVISED PER ECR-16-017870	20APR2017	BDA	MZ



- 1 PARTS PACKAGED UNASSEMBLED.
- 2 CABLE CLAMPING AREA ADJUSTABLE FROM .004 TO .055 SQ IN BY REVERSING CLAMPING INSERTS.
- 3 .329 MAXIMUM CABLE OUTSIDE DIAMETER.
- 4 BULK PACKAGED KITS TO BE ORDERED IN MULTIPLES OF 800 ONLY.
- 5 OBSOLETE PART NUMBER.
- 6 STAINLESS STEEL (NON MAGNATIC).
- 7 CABLE CLAMP WITH NON-MAGNETIC STAINLESS STEEL SCREWS.
- 8 ZINC PLATED STEEL, NON-HEXAVALENT CHROMATE.

- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 10 SPECIAL PACKAGING CONSISTING OF 1 KIT PER INDIVIDUAL BAG, 20 INDIVIDUAL BAGS PER LARGER BAG, 5 LARGER BAGS PER SHIPPER BOX.

OBSOLETE	<div>10</div>	<div>8</div>	$.50 \pm .05$	#5-20	2-206062-0
OBSOLETE	<div>7</div> <div>4</div> BULK	<div>6</div>	$.50 \pm .05$	#5-20	1-206062-9
	<div>4</div> BULK	<div>8</div>	$.50 \pm .05$	#5-20	1-206062-7
	INDIVIDUAL	<div>8</div>	$.38 \pm .05$	#5-20	1-206062-6
	<div>4</div> BULK	<div>8</div>	$.38 \pm .05$	#5-20	1-206062-5
	INDIVIDUAL	<div>8</div>	$.50 \pm .05$	#5-20	1-206062-4
	INDIVIDUAL	<div>8</div>	$.62 \pm .05$	#5-20	1-206062-3
	<div>7</div> INDIVIDUAL	<div>6</div>	$.50 \pm .05$	#5-20	1-206062-2
SUPERSEDED BY 1-206062-3	INDIVIDUAL	<div>8</div>	$.62 \pm .05$	#5-20	1-206062-1
<div>9</div> OBSOLETE	SMALL PACK	<div>8</div>	$.38 \pm .05$	#5-20	1-206062-0
AMP BRAZIL USE ONLY	INDIVIDUAL		$12\text{mm} \pm .0$	3mm-20	<div>5</div> 206062-9
AMP BRAZIL USE ONLY	INDIVIDUAL		$10\text{mm} \pm .0$	3mm-20	<div>5</div> 206062-8
SUPERSEDED BY 1-206062-7	<div>4</div> BULK	<div>8</div>	$.50 \pm .05$	#5-20	206062-4
SUPERSEDED BY 1-206062-4	INDIVIDUAL	<div>8</div>	$.50 \pm .05$	#5-20	206062-3
SUPERSEDED BY 1-206062-5	<div>4</div> BULK	<div>8</div>	$.38 \pm .05$	#5-20	206062-2
SUPERSEDED BY 1-206062-6	INDIVIDUAL	<div>8</div>	$.38 \pm .05$	#5-20	206062-1
PACKAGING		SCREW FINISH	SCREW LENGTH	SCREW TYPE	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

MATERIAL THERMOPLASTIC

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH -

DWN A GRAFF 4/29/91

CHK W.G.LENKER 7-22-92

APVD -

PRODUCT SPEC -

APPLICATION SPEC -

WEIGHT -

NAME

CABLE CLAMP KIT, STANDARD, SHELL SIZE 11, CPC

SIZE A3

CAGE CODE 00779

DRAWING NO C-206062

RESTRICTED TO -

CUSTOMER DRAWING

SCALE NTS

SHEET 1 OF 1

REV W

STE

TE Connectivity

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[206062-1](#)