



REVISIONS

LTR	DESCRIPTION	DATE	APPROVED
-----	-------------	------	----------

If this document is printed it becomes uncontrolled.
Check for the latest revision.



AS SUPPLIED



AFTER UNRESTRICTED RECOVERY

TABLE OF DIMENSIONS

PART NUMBER	H		J			P ±10% b	R REF b	S REF b	T REF b	U REF b	JO ±10% b	W ±20% b
	-3, -4, -12 MIN a	MAX b	-3, -4 MIN a	-12 MIN a	MAX b							
222D 121-X-60	.92	.41	.92	.49	.22	.84	.89	.65	.12	.040	.23	.05
222D 132-X-60	1.12	.56	1.12	.58	.26	1.33	1.07	.76	.12	.040	.65	.06
222D 142-X-60	1.22	.70	1.22	.63	.28	1.44	1.22	.83	.12	.040	.50	.07
222D 152-X-60	1.42	.88	1.42	.73	.33	1.72	1.38	.90	.12	.040	.57	.07
222D 163-X-60	1.68	1.11	1.68	.87	.39	2.11	1.73	1.14	.12	.065	.69	.08
222D 174-X-60	2.04	1.38	2.04	1.39	.62	3.07	2.08	1.32	.12	.065	1.32	.13
222D 185-X-60	2.60	1.75	2.60	1.80	.80	3.84	2.60	1.64	.12	.080	1.58	.15
222D 196-X-60	3.22	2.38	3.22	2.25	1.00	4.64	3.30	2.03	.12	.080	1.50	.16

NOTES:


- ALL DIMENSIONS ARE IN INCHES
- DIMENSIONS APPEARING IN TABLE ARE AS FOLLOWS:
a - AS SUPPLIED
b - AFTER UNRESTRICTED RECOVERY
- PARTS SHALL HAVE COLOR STRIPE .12 WIDE X 360° AROUND OUTSIDE SURFACE APPROX. AS SHOWN AND MUST MEET REQUIREMENTS SET FORTH IN MS-3117 COLORS SHALL BE AS FOLLOWS:

DASH NO.	COLOR
-3	WHITE
-4	RED
-12	YELLOW

- COATING IS OPTIONAL FOR -3 AND -4 MATERIALS ONLY. AS SUPPLIED DIMENSIONS APPEARING IN TABLE ARE FOR UNCOATED PARTS. WHEN COATING IS ADDED, ENTRY DIAMETERS WILL BE REDUCED BY .06 MAX. PARTS WILL BE COATED WITH S-1017 ADHESIVE WHEN SPECIFIED AS: 222D1XX-X-60/42

SPECIFICATION CONTROL DRAWING (LIMITED DISTRIBUTION)

ORDERING INFORMATION:



THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF RAYCHEM CORPORATION, AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE, OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY RAYCHEM CORPORATION IS PROHIBITED.	DRAWN	SEAN MCGARRY	Raychem	RAYCHEM CORPORATION 300 CONSTITUTION DRIVE MENLO PARK, CALIFORNIA 94025		
	CHECKED	SJS		TITLE	BOOT, 90° WITH LIP THINWALL	
	DESIGN APPROVED	S. J. S. 11-13-86	FSCM CODE NO.	DWG NO.	222D121-X-60 THRU 222D196-X-60	
	APPROVED BY		06090	DATE	SHEET, OF,	
	MANUFACTURING	11/13/86	SIZE B			
	QUALITY CONTROL	11/13/86				
	SPECIFICATION	11/13/86				
TECHNICAL SERVICES	11/13/86					
PRODUCT MANAGEMENT	11/13/86					

DO NOT SCALE THIS DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[222D142-4-60-0](#)