



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 <sub>0</sub>	RELEASED	5-10-79	GMH
01 <sub>2</sub>	REDRAWN ON CAD PER ECN 88-0678	M.Y. 4-4-89	<i>RJA</i> RCM
B	PER EC 0U20-0615-00	20SEP01	<i>C. Hoang</i> 20SEP01

HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	GOLD PLATE PER MIL-G-45204 OVER NICKEL PLATE PER QQ-N-290
COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER ASTM A380
DIELECTRIC	TFE FLUOROCARBON PER MIL-P-19468 AND FED SPEC L-P-403	N/A
CENTER CONTACT	BRASS PER ASTM-B-16, HALF HARD	GOLD PLATE PER MIL-G-45204
RETAINING RING	BERYLLIUM COPPER PER QQ-C-533	N/A
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
COMPONENT	MATERIAL	FINISH

CABLE ENTRY DIAMETER MINIMUM	
HOUSING	.142
CONTACT	.038

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES  
TOLERANCE ON  
FRAC. DEC. ANGLES  
± 1/64 ±.005 ± °

These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.

DRAWN BY D M DATE 3-27-79  
CHECKED BY RMF 5-3-79  
APP'D BY GMH 5-10-79

USE ASS'Y PROCEDURE

NO. AP. 37-001

AMP Incorporated  
140 Fourth Avenue  
Waltham, MA 02451-7599

**AMP**

TITLE 18 GHz OST CABLE PLUG DIRECT SOLDER ATTACH.

SIZE B	CODE IDENT NO. 26805	3701-7941-02	REV 01 <sub>2</sub>
SCALE 5:1		SHEET 1 OF 1	

NOTES:  
1. DESIGNED FOR USE WITH .141 SEMI-RIGID CABLE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1058694-1](#)