

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2016

© COPYRIGHT 2016 BY -

ALL RIGHTS RESERVED.

REVISIONS

| P | LTR | DESCRIPTION                 | DATE      | DWN | APVD |
|---|-----|-----------------------------|-----------|-----|------|
|   | H   | FIRST ISSUE (ECR-16-007013) | 12MAY2016 | DC  | DC   |
|   |     |                             |           |     |      |
|   |     |                             |           |     |      |

19.9 REF  
15.5 REF  
7.9  
8.7  
21.7±0.2 PITCH  
Ø6.35±0.15

0.8 RAW MAT. THK.  
4.1  
2.4  
2.4

SECTION D-D

SECTION C-C


5.0  
4.4

4.0  
3.7

WIRE RANGE 0.52-1.31 mm<sup>2</sup> [20-16 AWG]  
INSULATION RANGE Ø2.54-3.56 mm [Ø.100"-.140"]

P/N 140544 AS SHOWN

SCALE 2:1

|                                                                     |  |                                  |                                                                                                       |                    |
|---------------------------------------------------------------------|--|----------------------------------|-------------------------------------------------------------------------------------------------------|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                              |  | DWN<br>D.CHIARELLI<br>12MAY2016  |  TE Connectivity |                    |
| DIMENSIONS:<br>mm                                                   |  | CHK<br>D.CHIARELLI<br>12MAY2016  |                                                                                                       |                    |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                              |  | APVD<br>D.CHIARELLI<br>12MAY2016 | NAME<br>-<br>RING TONGUE                                                                              |                    |
| 0 PLC ±<br>1 PLC ±0.4<br>2 PLC ±<br>3 PLC ±<br>4 PLC ±<br>ANGLES ±° |  | PRODUCT SPEC<br>-                | APPLICATION SPEC<br>114-2084                                                                          |                    |
| MATERIAL<br>BRASS                                                   |  | FINISH<br>TIN                    | WEIGHT<br>-                                                                                           | RESTRICTED TO<br>- |
|                                                                     |  | CUSTOMER DRAWING                 | SCALE<br>5:1                                                                                          | SHEET<br>1 OF 1    |
|                                                                     |  |                                  |                                                                                                       | REV<br>H           |

1470-19 (3/13)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[140544](#)