



NOTE:
1. MATERIAL :
HOUSING : THERMOPLASTIC UL94V-0, WHITE COLOR.





34.0	32.5	30.0	32	3-1470107-2
32.0	30.5	28.0	30	3-1470107-0
30.0	28.5	26.0	28	2-1470107-8
28.0	26.5	24.0	26	2-1470107-6
26.0	24.5	22.0	24	2-1470107-4
24.0	22.5	20.0	22	2-1470107-2
22.0	20.5	18.0	20	2-1470107-0
20.0	18.5	16.0	18	1-1470107-8
18.0	16.5	14.0	16	1-1470107-6
16.0	14.5	12.0	14	1-1470107-4
14.0	12.5	10.0	12	1-1470107-2
12.0	10.5	8.0	10	1-1470107-0
10.0	8.5	6.0	8	1470107-8
8.0	6.5	4.0	6	1470107-6
DIM C	DIM B	DIM A	POS.	PART NUMBER

DIMENSION : 0 PLC ± 1 PLC ±0.30 2 PLC ±0.20 3 PLC ±0.10 ANGLES ±°	DWN O. HU 12-AUG-2003	TE Connectivity NAME 2.0 MM PITCH CRIMP HOUSING		
	CHK A. WU 12-AUG-2003			
MATERIAL SEE NOTE	APVD J. CHENG 12-AUG-2003	PRODUCT SPEC 108-57217		
FINISH SEE NOTE	QUALIFICATION TEST REPORT 501-57218			
WEIGHT		LOC DW	SIZE A ₃	DRAWING NO C-1470107
		SCALE --	SHEET 1 OF 2	


A1	REVISION RECORD	REVISD PER ECO-11-005301	RK HMR	5APR11
LTR	ECO	DWN CHK	DATE	

POLY BAG



CARTON
470mm(L)X 340 mm(W)X 178mm(H)
(FOR P/N 0-1470107-6~1-1470106-6)
470mm(L)X 340 mm(W)X 365mm(H)
(FOR P/N 1-1470107-8~3-1470106-2)

20,000	1000	3-1470107-2
20,000	1000	3-1470107-0
20,000	1000	2-1470107-8
24,000	1000	2-1470107-6
26,000	1000	2-1470107-4
30,000	1000	2-1470107-2
30,000	1000	2-1470107-0
36,000	1000	1-1470107-8
20,000	1000	1-1470107-6
20,000	1000	1-1470107-4
25,000	1000	1-1470107-2
30,000	1000	1-1470107-0
40,000	1000	1470107-8
50,000	1000	1470107-6
APQ (PCS/CARTON)	PPQ (PCS/BAG)	PART NUMBER

DIMENSION : 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± ANGLES ±°	DWN	O. HU 12-AUG-2003	 TE Connectivity
	CHK	A. WU 12-AUG-2003	
MATERIAL SEE NOTE	APVD	J. CHENG 12-AUG-2003	NAME 2.0 MM PITCH CRIMP HOUSING
	PRODUCT SPEC		
FINISH SEE NOTE	APPLICATION SPEC		LOC DW
	WEIGHT		SCALE
		SIZE A ₃	DRAWING NO C-1470107
		REV A1	SHEET 2 OF 2

LTR	REVISION RECORD	SEE SHEET 1.	ECO	DWN	CHK	DATE
-----	-----------------	--------------	-----	-----	-----	------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2-1470107-8](#)