


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
ES	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B2	REVISED PER ECO-11-005033	24MAR11	RK	HMR



- NOTES:
- 1 MATERIAL : 66 NYLON (UL94V-0)
 - 2. PRODUCT SPEC.: 108-5408
 - 3. APPLICATION SPEC.: 114-5179
 - 4 7-179228-3 WAS OBSOLETE.
 - 5 CAVITY NUMBER LOCATED. (OPTIONAL)



7-179228-5	5-179228-5	3-179228-5	1-179228-5	15	28	30.8	32.0
7-▲ -4	5-▲ -4	3-▲ -4	1-▲ -4	14	26	28.8	30.0
7-▲ -3	5-▲ -3	3-▲ -3	1-▲ -3	13	24	26.8	28.0
7- -2	5- -2	3- -2	1- -2	12	22	24.8	26.0
7- -1	5- -1	3- -1	1- -1	11	20	22.8	24.0
7- -0	5- -0	3- -0	1- -0	10	18	20.8	22.0
6- -9	4- -9	2- -9		9	16	18.8	20.0
6- -8	4- -8	2- -8		8	14	16.8	18.0
6- -7	4- -7	2- -7		7	12	14.8	16.0
6- -6	4- -6	2- -6		6	10	12.8	14.0
6- -5	4- -5	2- -5		5	8	10.8	12.0
6- -4	4- -4	2- -4		4	6	8.8	10.0
6- -3	4- -3	2- -3		3	4	6.8	8.0
6-179228-2	4-179228-2	2-179228-2	179228-2	2	2	4.8	6.0
BLACK	YELLOW	BLUE	NATURAL	POS	A	B	C
PART NUMBER							

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN T.FURUYA 12NOV1993
 CHK S.KUBOUCHI 15NOV1993
 APVD S.KUBOUCHI 15NOV1993

STE TE Connectivity

CRIMP TYPE II RECEPTACLE HOUSING
 (AMP CT CONNECTOR 2mm PITCH)

NAME

GENERAL TOLERANCE
 0 < * ≤ 10 : ±0.2
 10 < * ≤ 30 : ±0.25
 30 < * ≤ 100 : ±0.3
 ANGLES : ±3°

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
 0 PLC ± -
 1 PLC ± -
 2 PLC ± -
 3 PLC ± -
 4 PLC ± -
 ANGLES ± 3°

MATERIAL SEE NOTE 1

FINISH -

APVD S.KUBOUCHI 15NOV1993

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

SIZE A3 CAGE CODE 00779 DRAWING NO C-179228 RESTRICTED TO -

CUSTOMER DRAWING SCALE NTS SHEET 1 OF 1 REV B2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[5-179228-4](#)