

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC ES	DIST 00	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED PER ECO-11-005033	24MAR11	RK	HMR



- NOTES:
- 1 MATERIAL : 66 NYLON (UL94V-0)
 - 2. PRODUCT SPEC.: 108-5408
 - 3. APPLICATION SPEC.: 114-5179
 - 4 7-179228-3 WAS OBSOLETE.
 - 5 CAVITY NUMBER LOCATED. (OPTIONAL)



7-179228-5	5-179228-5	3-179228-5	1-179228-5	15	28	30.8	32.0
7-▲	5-▲	3-▲	1-▲	14	26	28.8	30.0
7-▲	5-▲	3-▲	1-▲	13	24	26.8	28.0
7-	5-	3-	1-	12	22	24.8	26.0
7-	5-	3-	1-	11	20	22.8	24.0
7-	5-	3-	1-	10	18	20.8	22.0
6-	4-	2-		9	16	18.8	20.0
6-	4-	2-		8	14	16.8	18.0
6-	4-	2-		7	12	14.8	16.0
6-	4-	2-		6	10	12.8	14.0
6-	4-	2-		5	8	10.8	12.0
6-	4-	2-		4	6	8.8	10.0
6-	4-	2-		3	4	6.8	8.0
6-179228-2	4-179228-2	2-179228-2	179228-2	2	2	4.8	6.0
BLACK	YELLOW	BLUE	NATURAL	POS	A	B	C

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN T.FURUYA 12NOV1993	TE Connectivity CRIMP TYPE II RECEPTACLE HOUSING (AMP CT CONNECTOR 2mm PITCH)			
DIMENSIONS: mm		CHK S.KUBOUCHI 15NOV1993				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S.KUBOUCHI 15NOV1993	NAME			
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± 3°		PRODUCT SPEC	SIZE			
MATERIAL		APPLICATION SPEC	CAGE CODE	DRAWING NO	RESTRICTED TO	
SEE NOTE 1		WEIGHT	A3	00779	C-179228	
GENERAL TOLERANCE		CUSTOMER DRAWING		SCALE	SHEET	REV
0 < * ≤ 10 : ±0.2 10 < * ≤ 30 : ±0.25 30 < * ≤ 100 : ±0.3 ANGLES : ±3°		SCALE NTS		SHEET 1 OF 1	REV B2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[7-179228-2](#)