

4


3

2

1

THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - A		ALL RIGHTS RESERVED.	
PROJECT	PRJ-14-000004825		
PART NO.	X-2322330-X		
DESCRIPTION	M12 D-4 CODE CABLE ASSY. (PLUG-PLUG) CAT 5E		
CUSTOMER	GENERAL MARKET		


REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
	A1	INTRODUCTION OF NEW DASH VARIANT, -99	24SEP2019	GK SE




M12 D-CODE CABLE ASSEMBLY  
(STRAIGHT CONNECTOR)

WIRING TABLE			
PIN		WIRE COLORS	PIN
1		YELLOW	1
2		WHITE	2
3		ORANGE	3
4		BLUE	4

SL.NO	CODE	ASSY. PART NO.	M12 CONNECTOR PART NO.	DESCRIPTION	CABLE TYPE	CABLE PART NO.	CABLE LENGTH "L" IN "m"	NO. OF POSITIONS
1	D4-CODE	9-2322330-9		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 0.5M CABLE			0.5	4
2	D4-CODE	2322330-1		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 1M CABLE			1.0	4
3	D4-CODE	2322330-2		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 1.5M CABLE			1.5	4
4	D4-CODE	2322330-3		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 2M CABLE			2.0	4
5	D4-CODE	2322330-4		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 2.5M CABLE			2.5	4
6	D4-CODE	2322330-5		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 3M CABLE			3.0	4
7	D4-CODE	2322330-6		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 3.5M CABLE			3.5	4
8	D4-CODE	2322330-7		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 4M CABLE			4.0	4
9	D4-CODE	2322330-8		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 4.5M CABLE			4.5	4
10	D4-CODE	2322330-9		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 5M CABLE			5.0	4
11	D4-CODE	1-2322330-0		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 5.5M CABLE			5.5	4
12	D4-CODE	1-2322330-1		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 6M CABLE			6.0	4
13	D4-CODE	1-2322330-2		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 6.5M CABLE			6.5	4
14	D4-CODE	1-2322330-3		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 7M CABLE			7.0	4
15	D4-CODE	1-2322330-4		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 7.5M CABLE			7.5	4
16	D4-CODE	1-2322330-5		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 8M CABLE			8.0	4
17	D4-CODE	1-2322330-6		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 8.5M CABLE			8.5	4
18	D4-CODE	1-2322330-7		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 9M CABLE			9.0	4
19	D4-CODE	1-2322330-8		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 9.5M CABLE			9.5	4
20	D4-CODE	1-2322330-9	2-2823445-1 (STRAIGHT)	M12 D-4-M CABLE ASSY. (PLUG-PLUG) 10M CABLE	TE CAT 5E CABLE	2320808-1	10.0	4
21	D4-CODE	2-2322330-0		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 10.5M CABLE			10.5	4
22	D4-CODE	2-2322330-1		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 11M CABLE			11.0	4
23	D4-CODE	2-2322330-2		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 11.5M CABLE			11.5	4
24	D4-CODE	2-2322330-3		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 12M CABLE			12.0	4
25	D4-CODE	2-2322330-4		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 12.5M CABLE			12.5	4
26	D4-CODE	2-2322330-5		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 13M CABLE			13.0	4
27	D4-CODE	2-2322330-6		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 13.5M CABLE			13.5	4
28	D4-CODE	2-2322330-7		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 14M CABLE			14.0	4
29	D4-CODE	2-2322330-8		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 14.5M CABLE			14.5	4
30	D4-CODE	2-2322330-9		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 15M CABLE			15.0	4
31	D4-CODE	3-2322330-0		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 15.5M CABLE			15.5	4
32	D4-CODE	3-2322330-1		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 16M CABLE			16.0	4
33	D4-CODE	3-2322330-2		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 16.5M CABLE			16.5	4
34	D4-CODE	3-2322330-3		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 17M CABLE			17.0	4
35	D4-CODE	3-2322330-4		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 17.5M CABLE			17.5	4
36	D4-CODE	3-2322330-5		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 18M CABLE			18.0	4
37	D4-CODE	3-2322330-6		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 18.5M CABLE			18.5	4
38	D4-CODE	3-2322330-7		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 19M CABLE			19.0	4
39	D4-CODE	3-2322330-8		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 19.5M CABLE			19.5	4
40	D4-CODE	3-2322330-9		M12 D-4-M CABLE ASSY. (PLUG-PLUG) 20M CABLE			20.0	4



SECTIONAL PICTORIAL VIEW OF THE CABLE



PICTORIAL VIEW

SL.NO.	PART NO.	DESCRIPTION	QTY
1	2-2823445-1	M12 D-CODED M-8 MALE CONNECTOR	2
2	2320808-1	TE CAT 5E CABLE (COLOR: BLUE)	METER (REF. TABLE)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN K 07JUL2017	TE Connectivity	
DIMENSIONS: mm		CHK KIRAN K 07JUL2017		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD E STELLINGA 07JUL2017	NAME M12 D-4-M CODE CABLE ASSEMBLY CAT 5E (PLUG-PLUG)	
0 PLC ± -		PRODUCT SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO	
1 PLC ± -		APPLICATION SPEC	A2 00779 C=2322330	
2 PLC ± -		WEIGHT	SCALE NTS SHEET 1 OF 1 REV A1	
3 PLC ± -		CUSTOMER DRAWING		
4 PLC ± -				
ANGLES ± -				
FINISH				

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2322330-7](#)