




THIS DRAWING IS UNPUBLISHED.		RELEASED FOR PUBLICATION	
© COPYRIGHT - TE Connectivity		ALL RIGHTS RESERVED.	
PROJECT	PRJ-14-000004825		
PART NO.	X-2322422-X		
DESCRIPTION	M12 D-4 CODE CABLE ASSY. (PLUG-PLUG) CAT 5E		
CUSTOMER	GENERAL MARKET		

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
A		INITIAL RELEASE	07JUL2017	KK ES



WIRING TABLE			
PIN	WIRE COLORS	PIN	
1	YELLOW	1	
2	WHITE	2	
3	ORANGE	3	
4	BLUE	4	

SL.NO	CODE	ASSY. PART NO.	M12 CONNECTOR 1 PART NO.	M12 CONNECTOR 2 PART NO.	DESCRIPTION	CABLE TYPE	CABLE PART NO.	CABLE LENGTH "L" IN "m"	NO. OF POSITIONS
1	D4-CODE	2322422-1			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 1M CABLE			1.0	4
2	D4-CODE	2322422-2			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 1.5M CABLE			1.5	4
3	D4-CODE	2322422-3			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 2M CABLE			2.0	4
4	D4-CODE	2322422-4			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 2.5M CABLE			2.5	4
5	D4-CODE	2322422-5			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 3M CABLE			3.0	4
6	D4-CODE	2322422-6			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 3.5M CABLE			3.5	4
7	D4-CODE	2322422-7			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 4M CABLE			4.0	4
8	D4-CODE	2322422-8			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 4.5M CABLE			4.5	4
9	D4-CODE	2322422-9			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 5M CABLE			5.0	4
10	D4-CODE	1-2322422-0			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 5.5M CABLE			5.5	4
11	D4-CODE	1-2322422-1			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 6M CABLE			6.0	4
12	D4-CODE	1-2322422-2			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 6.5M CABLE			6.5	4
13	D4-CODE	1-2322422-3			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 7M CABLE			7.0	4
14	D4-CODE	1-2322422-4			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 7.5M CABLE			7.5	4
15	D4-CODE	1-2322422-5			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 8M CABLE			8.0	4
16	D4-CODE	1-2322422-6			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 8.5M CABLE			8.5	4
17	D4-CODE	1-2322422-7			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 9M CABLE			9.0	4
18	D4-CODE	1-2322422-8			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 9.5M CABLE			9.5	4
19	D4-CODE	1-2322422-9	2-2823445-1 (STRAIGHT)	1-2823588-3 (RIGHT ANGLE)	M12 D-4-M CABLE ASSY. (PLUG-PLUG) 10M CABLE	TE CAT 5E CABLE	2320808-1	10.0	4
20	D4-CODE	2-2322422-0			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 10.5M CABLE			10.5	4
21	D4-CODE	2-2322422-1			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 11M CABLE			11.0	4
22	D4-CODE	2-2322422-2			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 11.5M CABLE			11.5	4
23	D4-CODE	2-2322422-3			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 12M CABLE			12.0	4
24	D4-CODE	2-2322422-4			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 12.5M CABLE			12.5	4
25	D4-CODE	2-2322422-5			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 13M CABLE			13.0	4
26	D4-CODE	2-2322422-6			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 13.5M CABLE			13.5	4
27	D4-CODE	2-2322422-7			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 14M CABLE			14.0	4
28	D4-CODE	2-2322422-8			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 14.5M CABLE			14.5	4
29	D4-CODE	2-2322422-9			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 15M CABLE			15.0	4
30	D4-CODE	3-2322422-0			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 15.5M CABLE			15.5	4
31	D4-CODE	3-2322422-1			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 16M CABLE			16.0	4
32	D4-CODE	3-2322422-2			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 16.5M CABLE			16.5	4
33	D4-CODE	3-2322422-3			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 17M CABLE			17.0	4
34	D4-CODE	3-2322422-4			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 17.5M CABLE			17.5	4
35	D4-CODE	3-2322422-5			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 18M CABLE			18.0	4
36	D4-CODE	3-2322422-6			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 18.5M CABLE			18.5	4
37	D4-CODE	3-2322422-7			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 19M CABLE			19.0	4
38	D4-CODE	3-2322422-8			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 19.5M CABLE			19.5	4
39	D4-CODE	3-2322422-9			M12 D-4-M CABLE ASSY. (PLUG-PLUG) 20M CABLE			20.0	4



SL.NO.	PART NO.	DESCRIPTION	QTY
1	2-2823445-1	M12 D-4 CODED MALE CONNECTOR	1
2	2320808-1	TE CAT 5E CABLE (COLOR: BLUE)	METER (REF. TABLE)
3	1-2823588-3	M12 D-4 CODED MALE 90° CONNECTOR	1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN 07JUL2017	
	0 PLC ± -	CHK 07JUL2017	
	1 PLC ± -	APVD 07JUL2017	
	2 PLC ± -	E STELLINGA	
	3 PLC ± -	PRODUCT SPEC	
MATERIAL	FINISH	APVD 07JUL2017	NAME
		APPLICATION SPEC	M12 D-4-M CODE CABLE ASSEMBLY CAT 5E (PLUG-PLUG)
		WEIGHT	SIZE
		CUSTOMER DRAWING	A2 00779
		SCALE	DRAWING NO
		NTS	C=2322422
		SHEET	RESTRICTED TO
		1 OF 1	-
		REV	A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[3-2322422-0](#)