

Thermofit Molded Parts

Specification Control Drawing

Part Number: 423A014
Description: Transition, Two 90° Side Breakouts

Notes:

- All dimensions are in $\frac{\text{Inches}}{\text{[Millimeters]}}$; $\frac{\text{lbs}}{\text{[gms]}}$
- Dimensions appearing in table are as follows:
a - as supplied
b - after unrestricted recovery
- Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
- Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.





Table of Dimensions

Part Number	H & J		K		L		P ± 10% b	R ± 10% b	S & T ± 10% b	U ± 10% b	HW & JW ± 20% b	KW ± 20% b	LW ± 20% b	Weight ± 10%
	Min. a	Max. b	Min. a	Max. b	Min. a	Max. b								
423A014	1.20 [30.5]	.60 [15.2]	.70 [17.8]	.35 [8.9]	.80 [20.3]	.40 [10.2]	4.60 [116.8]	2.10 [53.3]	1.50 [38.1]	1.25 [31.8]	.10 [2.54]	.06 [1.52]	.07 [1.78]	.073 [33.11]

If this document is printed it becomes uncontrolled.
 Check for the latest revision.

Raychem
 Raychem Corporation
 300 Constitution Drive
 Menlo Park, California 94025
 415) 361 6055

Revision: **D**
 Date: **4-2-84**

Part Number: 423A014
Description: Transition, Two 90° Side Breakouts

Thermofit Molded Parts Specification Control Drawing

Part Number: 423A014
Description: Transition, Two 90°
Side Breakouts

Compatibility Chart

Material Dash No.	Material Description	RT Spec	Coating Slash No.	Coating S No.	Coating Description
- 3	Polyolefin, semi-rigid	RT-301	/42	S-1017	Adhesive
- 4	Polyolefin, flexible	RT-1304	/42	S-1017	Adhesive
- 5	Neoprene	RT-501	/42	S-1017	Adhesive
- 6	Silicone, flame retarded	RT-602	N/A		
- 12	Viton	RT-1312	N/A		
- 25	Elastomer, fluid resistant	RT-1325	N/A		

Ordering Information:

423A0XX — XX — XX / XXX

Base part number

Material dash number
(see compatibility chart)

Modification number
(if necessary, see front of SCD binder
for a complete modification list)

Adhesive slash number
(if necessary, see compatibility chart)

This drawing is subject to change without notice; consult your nearest field representative for current revision.

Raychem

Raychem Corporation
300 Constitution Drive
Menlo Park, California 94025
415) 361 6055

If this document is printed it becomes uncontrolled.
Check for the latest revision.

Revision: **D**
Date: **4-2-84**

Part Number: 423A014
Description: Transition, Two 90°
Side Breakouts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[820063-000](#)