


REVISIONS					
P	LTR	DESCRIPTION	DATE	DRN	APVD
J		REVISED PER ECO-21-005295	05MAY2021	KK	AK



- 1. CHARACTERISTIC IMPEDANCE: 100±10 OHMS(MEASURED DIFFERENTIALLY)
- 2. LABEL INFORMATION FOR 25GIG PNS (-1 THRU -8): -1 SHOWN

	2821223-[]	TE LOGO & PART NUMBER
	0.5M - 28AWG	LENGTH - CABLE GAGE
	PPPPPLYWWSSS	SERIAL NUMBER: INCLUDES PN, MANUFACTURING LOCATION, AND DATE CODE
		SERIAL NUMBER BARCODE
- 3. SEE SHEET 2 FOR WIRING SCHEMATIC.
- 4. ROHS COMPLIANCE: PRODUCT AND PROCESSING MEETS REQUIREMENTS OF TE CONNECTIVITY SPECIFICATION TEC-138-702.
- 5. TEST IN ACCORDANCE WITH IEEE802.3by.
- 6. LABEL INFORMATION FOR 56GIG PNS (-41 THRU -46): -41 SHOWN


	4-2821223-[]	TE LOGO & PART NUMBER
	0.5M - 28AWG	LENGTH - CABLE GAGE
	PPPPPLYWWSSS	SERIAL NUMBER: INCLUDES PN, MANUFACTURING LOCATION, AND DATE CODE
		SERIAL NUMBER BARCODE
- 7. DASH NUMBER 41 THRU 46 CONFORM TO 56G, PAM-4 IEEE802.3CD PERFORMANCE REQUIREMENTS.

STANDARD	WIRE GAGE	L	PART NO
7	28	300 ⁺⁵⁰ ₋₀	4-2821223-6
	28	2500 ⁺⁸⁰ ₋₀	4-2821223-5
	28	2000 ⁺⁸⁰ ₋₀	4-2821223-4
	28	1500 ⁺⁵⁰ ₋₀	4-2821223-3
	28	1000 ⁺⁵⁰ ₋₀	4-2821223-2
	28	500 ⁺⁵⁰ ₋₀	4-2821223-1
5	28	4000 ⁺⁸⁰ ₋₀	2821223-8
	28	3500 ⁺⁸⁰ ₋₀	2821223-7
	28	3000 ⁺⁸⁰ ₋₀	2821223-6
	28	2500 ⁺⁸⁰ ₋₀	2821223-5
	28	2000 ⁺⁸⁰ ₋₀	2821223-4
	28	1500 ⁺⁵⁰ ₋₀	2821223-3
	28	1000 ⁺⁵⁰ ₋₀	2821223-2
	28	500 ⁺⁵⁰ ₋₀	2821223-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DIN T. SMITH 08OCT2015	TE Connectivity Ltd.
0. PLC ± -	1. PLC ± -	CHK C. POGASH 08OCT2015	
2. PLC ± -	3. PLC ± -	APVD G. POGASH 08OCT2015	NAME CABLE ASSY, 28 AWG, SFP+ TO SFP+, 28GIG
4. PLC ± -	ANGLES ± -	PRODUCT SPEC	APPLICATION SPEC
MATERIAL	FINISH	SIZE A1	RESTRICTED TO
		WEIGHT	SCALE 1:1
		CUSTOMER DRAWING	SHEET 1 OF 2

REVISIONS				
REV	DATE	DESCRIPTION	BY	APP'D
-	-	SEE SHEET 1	-	-



THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN T.SMITH 08OCT2015		 TE Connectivity Ltd.	
DIMENSIONS: mm		CHK C.POGASH 08OCT2015			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APP'D C.POGASH 08OCT2015		NAME CABLE ASSY,28 AWG,SFP+ TO SFP+, 28GIG	
0. PLC ± -		PRODUCT SPEC		APPLICATION SPEC	
1. PLC ± -		SIZE A1		CAGE CODE 00779	
2. PLC ± -		DRAWING NO. C=2821223		RESTRICTED TO	
3. PLC ± -		WEIGHT		SCALE 1:1	
4. PLC ± -		CUSTOMER DRAWING		SHEET 2 OF 2	
ANGLES ± -		FINISH		REV J	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[4-2821223-5](#)