

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
E4		REVISED ECR-21-107353	14JUL21	T.Q	N.S

回路No. 1
CIRCUIT No. 1

注記

- 適用電線範囲: AWG #26
被覆外径: $\phi 0.8\text{mm} \sim \phi 0.95\text{mm}$
- 材料: ハウジング-ガラス入りナイロン UL94V-0、色: グレー、青
コンタクト-錫めっき済み、りん青銅
- ハウジング ロック:
2極は、1箇所 3~20極は、2箇所
- ゲート口は左付きと右付きが存在する。(2極品を除く)

NOTES:

- APPLICABLE WIRE SIZE: AWG #26
INSULATION DIA RANGE: $\phi 0.8\text{mm} \sim \phi 0.95\text{mm}$
- MATERIAL:
HOUSING: NYLON(G.F.) UL94V-0, COLOR: GRAY, BLUE
CONTACT: PRE-TIN PHOS-BRONZE
- HOUSING LOCK:
2 POSITION - SINGLE LOCK
3 TO 20 POSITIONS - DOUBLE LOCK
- CONNECTOR HAVE THE GATE LEFT SIDE AND RIGHT SIDE. (EXCEPT 2Pos.)

キャビティ マーク
CAVITY MARK

ピッチ
PITCH

トレード マーク
TRADE MARK

2 極
2 POSITION

DIMENSIONS: 単位: 毫 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED 一般公差 10 μ : ± 0.2 30 μ >10 : ± 0.25 100 μ >30 : ± 0.3 ANGLE : $\pm 3^\circ$	DWN	12. JUL '96	WIRE RANGE 適合電線断面積 0.08mm ² - 0.14mm ²	INSULATION DIA 被覆外径 $\phi 0.8\text{mm} \sim \phi 0.95\text{mm}$	
		CHK	12. JUL '96	TE Connectivity		
MATERIAL 材料 SEE NOTE 2 注記2参照	FINISH 仕上 SEE NOTE 2 注記2参照	APVD	12. JUL '96			NAME 名称 AMP Mini Common Terminated (CT) Connector 1.5mm PITCH MT RECEPTACLE ASSEMBLY
		PRODUCT SPEC	J. TANIGAWA	SIZE	CAGE CODE	DRAWING NO 番号
		APPLICATION SPEC 取付適用規格	108-5525	A3	00779	C=353293
		WEIGHT 重量 SEE TABLE 表参照	114-5223	SCALE 尺度 NON		
CUSTOMER DRAWING			SHEET 張数 1 OF 2			
			REV 改訂 E4			

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			


0.97	31.5	30.5	28.5	20	7-353293-0	4-353293-0	2-353293-0
0.92	30.0	29.0	27.0	19	6-353293-9	3-353293-9	1-353293-9
0.87	28.5	27.5	25.5	18	6-353293-8	3-353293-8	1-353293-8
0.83	27.0	26.0	24.0	17	6-353293-7	3-353293-7	1-353293-7
0.78	25.5	24.5	22.5	16	6-353293-6	3-353293-6	1-353293-6
0.73	24.0	23.0	21.0	15	6-353293-5	3-353293-5	1-353293-5
0.68	22.5	21.5	19.5	14	6-353293-4	3-353293-4	1-353293-4
0.64	21.0	20.0	18.0	13	6-353293-3	3-353293-3	1-353293-3
0.59	19.5	18.5	16.5	12	6-353293-2	3-353293-2	1-353293-2
0.54	18.0	17.0	15.0	11	6-353293-1	3-353293-1	1-353293-1
0.49	16.5	15.5	13.5	10	6-353293-0	3-353293-0	1-353293-0
0.45	15.0	14.0	12.0	9	5-353293-9	2-353293-9	353293-9
0.40	13.5	12.5	10.5	8	5-353293-8	2-353293-8	353293-8
0.35	12.0	11.0	9.0	7	5-353293-7	2-353293-7	353293-7
0.30	10.5	9.5	7.5	6	5-353293-6	2-353293-6	353293-6
0.26	9.0	8.0	6.0	5	5-353293-5	2-353293-5	353293-5
0.21	7.5	6.5	4.5	4	5-353293-4	2-353293-4	353293-4
0.16	6.0	5.0	3.0	3	5-353293-3	2-353293-3	353293-3
0.11	4.5	3.5	1.5	2	5-353293-2	2-353293-2	353293-2
WEIGHT (g)	C	B	A	Pos.	BLUE	BLACK	GRAY
	寸法 DIMENSIONS				製品型番 P/N		


RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT

DIMENSIONS: 単位: ㎜ mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 10 > : ±0.2 30 > : ±0.25 100 > : ±0.3 ANGLE : ±3°	DWN T. FURUYA 12. JUL '96 CHK J. TANIGAWA 12. JUL '96 APVD	WIRE RANGE 絶縁電線断面積 0.08mm ² -0.14mm ²	INSULATION DIA 被覆外径 ∅0.8mm-∅0.95mm	
	MATERIAL SEE SHEET 1 OF 2 材料 枚目参照	FINISH SEE SHEET 1 OF 2 仕上 枚目参照	 TE Connectivity	
	NAME 名称 AMP Mini Common Terminated (CT) Connector 1.5mm PITCH MT RECEPTACLE ASSEMBLY			
	PRODUCT SPEC 製品規格 108-5525	APPLICATION SPEC 取付運用規格 114-5223	SIZE A4	CAGE CODE 00779
WEIGHT SEE TABLE 表参照	CUSTOMER DRAWING	SCALE 尺度 NON	SHEET 2 OF 2	REV E4



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[353293-2](#)