



Thermofit[®] Molded Parts

Specification Control Drawing

Part Number: 422A813
Description: Transition, Two 90° Side Breakouts

Notes:

- All dimensions are in $\frac{\text{Inches}}{\text{[Millimeters]}}$; $\frac{\text{lbs}}{\text{[gms]}}$
- Dimensions appearing in table are as follows:
 a - as supplied
 b - after unrestricted recovery
- Coating is optional. As supplied dimensions appearing in table are for uncoated parts. When coating is added, entry diameters will be reduced by .06 max.
- Molding ports are optional. When -00 modification number is specified molding ports will be located as shown.
- Weight shown in table of dimensions is based on polyolefin part.



Part Number	H & J		K & L			P ± 10%	R ± 10%	S ± 10%	T ± 10%	U ± 10%	PP ± 10%	HW & JW ± 20%	W ± 20%	Weight ± 10%
	Min	Max	Min	Min	Max									
	3, 4, 12, 25 a	b	3, 4 25 a	12 a	b									
422A813	1.00 [25,4]	.60 [15,2]	.38 [9,7]	.28 [7,1]	.20 [5,1]	3.62 [91,9]	1.56 [39,6]	1.06 [26,9]	.50 [12,7]	.30 [7,6]	.30 [7,6]	.08 [2,03]	.05 [1,27]	.030 [13,6]

Raychem

Raychem Corporation
 300 Constitution Drive
 Menlo Park, California 94025
 415) 361 6055

If this document is printed it becomes uncontrolled.
 Check for the latest revision.

Revision: F
 Date: 7-25-85

Part Number: 422A813
Description: Transition, Two 90° Side Breakouts

Thermofit[®] Molded Parts Specification Control Drawing


Part Number: 422A813
Description: Transition, Two 90°
Side Breakouts

Compatibility Chart					
Material Dash No.	Material Description	RT Spec	Coating Slash No.	Coating S No.	Coating Description
- 3	Polyolefin, semi-rigid	RT-301	/42; /86; /87	S-1017; S-1048; S-1052	Adhesive
- 4	Polyolefin, flexible	RT-1304	/42; /86; /87	S-1017; S-1048; S-1052	Adhesive
- 12	Viton	RT-1312	N/A		
- 25	Elastomer, fluid resistant	RT-1325	N/A		

If this document is printed it becomes uncontrolled.
Check for the latest revision.

Ordering Information:

422A8XX — XX — XX / XXX



This drawing is subject to change without notice; consult your nearest field representative for current revision.

Raychem

Raychem Corporation
300 Constitution Drive
Menlo Park, California 94025
415) 361 6055

Revision: **F**
Date: **7-25-85**

Part Number: 422A813
Description: Transition, Two 90°
Side Breakouts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[422A813-25-0](#)