

0145

A P P L I C A T O R S

=====

MARK (N/A/L/C)

LOGNUMBER: 8 - 0878534 - 4 DESCRIPTION: MQC-F-APPL.

REVISION: F REV.-DATE : 04.12.07 INSTRUCTION: EF
ALREADY PRODUCED: N CONTROLL-GAUGE:
FEED: 1651 MM EXPLODED-VIEW: 0-8781048-3
INSULATION SPAN: 279 - 432 MM SKINNING LENGTH: MM

TEXT:

HAND/MECH.VORSCH. POS.161 EINSCHLEIFEN NACH 4-562364-3 REV.F E
CR-07-029150

REPLACEMENT: 00

USED FOR FOLLOWING CONTACTS (JUST THE BASE NUMBER IS GIVEN)

- 0042199 - .205 FLAG FAST REC IS 20-16 BR
- 0042458 - .205 FLAG FAST REC 20-16 BR
- 0042486 - .187 FLAG FAST RCPT 20-16 BR
- 0042618 - .187 FLAG FAST RCPT 20-16 BR
- 0042711 - 205 FLAG FAST REC 20-16 BR
- 0042809 - 205 FLAG FAST REC 20-16 BR
- 0060219 - RECP, 187 SERIES FLAG FASTON
- 0060657 - 187 FLG FAST REC 20-16 BR
- 0061401 - 187 FLG FAST REC 20-16 BR
- 0062591 - 187 FLG FAST RCPT 20-16 TPBR
- 0063748 - RCPT 187 FLG FASTON 0126 BR
- 0150634 - FLAG FASTON RECPT
- 0150680 - FLAG FASTON RECPT.
- 0150699 - FLAG FASTON RECEPTACLE

1451

B I L L O F M A T E R I A L

=====

APPLICATOR: 8 - 0878534 - 4 DESCRIPTION: MQC-F-APPL.

Table with 7 columns: PART - NO, DESCRIPTION, NUMBER, NO., MARKER, CODE, STATUS. It lists various components like WIRE CRIMPER, INSULATION CRIMPER, BUTTON CRIMPER SPACER, ANVIL, RETAINING, BLADE, SHEAR, ANVIL-REVERSIBLE, FRONT SHEAR PLATE, ANVIL INSERT, PLATE, REAR SHEAR, SPRING, COMPRESSION, POSITIONER, TERM. (.200), SPRING, COMPRESSION, VORDERE STREIFENF., GUIDE, REAR STRIP, DRAG, STOCK, PIN, DOWEL, SPRING, COMPRESSION, SPRING PRESSURE BLOCK, STABILIZER BLOCK, BAR HINGE, PLATE, BASE, PIN, HINGE.

0-0021030-2	PIN,DOWEL	001	029		
1-0022354-8	STUD	002	030		
0-0454569-1	MOUNT DRAG	001	031		
0-0690573-1	SPRING ADJUSTING SPACER	001	032		
3-0023846-5	SPRING,DIE	001	034		
0-0022480-5	WASHER,WAVE SPRING	001	036		
0-0690170-1	SPRING-COMPRESSION	002	039		
0-0023241-6	BALL, STEEL	002	040		
0-0690125-1	SHIM SUB-ASSY	001	043		
0-0690191-1	NYLON PLUG	001	045		
0-0690578-1	INSULATION-ADJ BLOCK	001	046		
0-0022353-8	SCREW,SHOULDER,SLOT HEAD	001	047		
0-0238015-1	CAM-TERM FEED	001	048		
3-0021002-5	SCREW,CAP,SOCKET,BUTTON HEA	001	049		
0-0240634-1	LEVER, TERMINAL FD	001	052		
0-0454568-2	FEED FINGER	001	053	F	?
0-0691499-1	SPRING-FEED FINGER	001	054		
0-0240624-1	PIN, FEED FINGER	001	055		
0-0458361-1	GUIDE-FEED ROD	001	056		
0-0455162-1	HOUSING-MACHINING	001	058		
0-0455164-1	CAP-RAM	001	059		
0-0240631-1	ROD, FEED	001	061		
0-0240658-1	ROLLER-CAM	001	062		
0-0240659-3	PIN-CAM ROLLER	001	063		
0-0240632-2	SCREW ADJUSTMENT	001	064		
0-0240629-1	BLOCK, PIVOT-MACHINING	001	065		
0-0240630-1	LEVER-INTERMEDIATE	001	066		
0-0240633-1	BUSHING	001	067		
0-0240626-1	SHAFT-PIVOT	001	068		
0-0240628-1	PLATE ADJUSTING	001	069		?
0-0022594-8	NUT,HEX,JAM	001	070		
0-0690603-1	SPRING ASSIST	002	072		
0-0458109-1	WASHER, SPL ADJUST PLATE	001	073		
1-0021000-9	SCREW,CAP,SOCKET HEAD	001	074		
0-0879626-1	RAMP	001	075		
2-0021008-9	SCREW,SET,SOC HD,CUP PT	001	076		
3-0021000-8	SCREW,CAP,SOCKET HEAD	004	102		
3-0021000-6	SCREW,CAP,SOCKET HEAD	002	104		
2-0021000-9	SCREW,CAP,SOCKET HEAD	004	106		
3-0021000-0	SCREW,CAP,SOCKET HEAD	002	107		
2-0021000-8	SCREW,CAP,SOCKET HEAD	002	109		
2-0021000-7	SCREW,CAP,SOCKET HEAD	002	110		
3-0021000-4	SCREW,CAP,SOCKET HEAD	001	111		
1-0023030-1	SCREW,CAP,SOC HD	002	112		
3-0021000-4	SCREW,CAP,SOCKET HEAD	002	114		
2-0022733-9	SCREW,CAP,SOC,BUT HD	004	116		
3-0021002-4	SCREW,CAP,SOCKET,BUTTON HEA	003	117		
2-0021002-1	SCREW,CAP,SOCKET,BUTTON HEA	001	119		
0-0021009-2	SCREW,SET,SOC HD,CUP PT	001	121		
8-0021007-5	SCREW,SET,SOC HD,CUP PT	001	123		?
4-0021006-0	SCREW,SET,SOC HD,CUP PT	002	124		?
3-0021012-1	SCREW,SET,SOC,FP	002	125		
0-0021061-9	SCREW,SET,SOCKET,CONE POINT	001	126		
1-0022202-7	NUT,HEX,JAM	001	127		
0-0021068-5	NUT,HEX,MACHINE SCREW	001	128		
0-0021022-3	NUT,HEX,SELF-LKG,THIN	002	129		
0-0021024-5	WASHER,SPG LOCK,REG	002	131		
0-0021024-4	WASHER,SPG LOCK,REG	004	132		
1-0021899-3	WASHER,FLAT	008	133		
1-0021030-3	PIN,DOWEL	001	138		
1-0021030-4	PIN,DOWEL	001	139		

1-0021030-2	PIN,DOWEL	001	140	
5-0021028-1	PIN,SLOTTED SPRING	001	142	
3-0021028-2	PIN,SLOTTED SPRING	001	144	
4-0021028-9	PIN,SLOTTED SPRING	002	145	
3-0021064-1	SCREW,MACHINE,SLOT RH	001	150	
0-0021045-3	RING,RETAINING,EXT CRESCENT	002	155	
0-0547882-1	WIRE-DISK	001	161	R
0-0562071-1	EINSTELLSCHEIBE-ISO	001	162	
0-0547843-1	SCHEIBE-OBEN	001	163	
0-0547844-1	SCHEIBE-UNTEN	001	164	
0-0653062-2	THRUST ELASTIC	001	165	
1-0542702-2	RAM	001	166	
0-0510495-6	M4X6 DIN551 KUNSTST	001	167	
2-0021012-9	SCREW,SET,SOC,FP	002	168	
0-0547847-2	STOESSEL-KOPF	001	169	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[8-878534-4](#)