

8

7

6

5

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—	SEE SHEET 1	—	—	—

OBSOLETE

11

9 10	8	64.01 [2.520]	65.91 [2.595]	24	25	7-103669-4
9 10	8	61.47 [2.420]	63.37 [2.495]	23	24	7-103669-3
9 10	8	58.93 [2.320]	60.83 [2.395]	22	23	7-103669-2
9 10	8	56.39 [2.220]	58.29 [2.295]	21	22	7-103669-1
9 10	8	53.85 [2.120]	55.75 [2.195]	20	21	7-103669-0
9 10	8	51.31 [2.020]	53.21 [2.095]	19	20	6-103669-9
9 10	8	48.77 [1.920]	50.67 [1.995]	18	19	6-103669-8
9 10	8	46.23 [1.820]	48.13 [1.895]	17	18	6-103669-7
9 10	8	43.69 [1.720]	45.59 [1.795]	16	17	6-103669-6
9 10	8	41.15 [1.620]	43.05 [1.695]	15	16	6-103669-5
9 10	8	38.61 [1.520]	40.51 [1.595]	14	15	6-103669-4
9 10	8	36.07 [1.420]	37.97 [1.495]	13	14	6-103669-3
9 10	8	33.53 [1.320]	35.43 [1.395]	12	13	6-103669-2
9 10	8	30.99 [1.220]	32.89 [1.295]	11	12	6-103669-1
9 10	8	28.45 [1.120]	30.35 [1.195]	10	11	6-103669-0
9 10	8	25.91 [1.020]	27.81 [1.095]	9	10	5-103669-9
9 10	8	23.37 [.920]	25.27 [.995]	8	9	5-103669-8
9 10	8	20.83 [.820]	22.73 [.895]	7	8	5-103669-7
9 10	8	18.29 [.720]	20.19 [.795]	6	7	5-103669-6
9 10	8	15.75 [.620]	17.65 [.695]	5	6	5-103669-5
9 10	8	13.21 [.520]	15.11 [.595]	4	5	5-103669-4
9 10	8	10.67 [.420]	12.57 [.495]	3	4	5-103669-3
9 10	8	8.13 [.320]	10.03 [.395]	2	3	5-103669-2
9 10	8	5.59 [.220]	7.49 [.295]	1	2	5-103669-1
REMARKS	PLATING	C	B	A	NO. OF POSN	PART NO.

11

OBSOLETE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
HOUSING: LCP,
CONTACTS: BRASS

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0. PLC
1. PLC
2. PLC
3. PLC
4. PLC
ANGLES

± -
± -
± -
± -
± -

0.13[.005]

SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
S. SHUEY
CHK
M. RIDER
APVD
M. RIDER

3-5-91
2-14-92
2-14-92

PRODUCT SPEC
108-25034
APPLICATION SPEC
114-25026
WEIGHT
—

SIZE
A1

CAGE CODE
00779

DRAWING NO
103669

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
4:1

SHEET
2

OF
2

REV
AD1

TE Connectivity

HDR ASSY, VERT, SR
2.54 .100 C/L 0.64 .025 SQ POST
WITH PLZN, AMPMODU MTE

4805 (1/15)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[103669-1](#)