

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

AP

-

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECN-23214009	23MAY2023	WLS	JS
	CI	REVISED PER ECN-24-266312	15MAY2024	WLS	JS

CAD
Pro-8DO NOT REVISE
EXCEPT BY CAD

19,9

7,3 MAX.

LOGO AND MANUFACTURING COUNTRY CODE

△ RAW MATERIAL ACC. TO SPEC. IEC 60335-1, GWEPT 750°C, WITHOUT FLAME.

6,0

2,8

5,5 MAX.

4,2 MAX.

	NATURAL	PA 6.6 UL94-V0 △	2-2133394-2
	NATURAL	PA6.6V0 OR PA6.6V0+PA6V0	2-2133394-1
OBSOLETE	AMARELO/YELLOW	PA 6.6 UL94-V2	1-2133394-4
	VERMELHO/RED	PA 6.6 UL94-V2	1-2133394-3
	PRETO/BLACK	PA 6.6 UL94-V2	1-2133394-2
	NATURAL/NATURAL	PA 6.6 UL94-V2	1-2133394-1
	NATURAL/NATURAL	POLIPROPILENO/POLYPROPYLENE	2133394-2
	PRETO/BLACK	POLIPROPILENO/POLYPROPYLENE	2133394-1
	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN H.C.CANTER 17AUG2011

CHK W.L.STEFANI 17AUG2011

APVD -

NAME

PRODUCT SPEC -

HOUSING, .187 SERIES, FASTON REC.

APPLICATION SPEC -

RESTRICTED TO -

WEIGHT -

SIZE A3 CAGE CODE 00779 DRAWING NO. C-2133394

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±
1 PLC	±0,5
2 PLC	±
3 PLC	±
4 PLC	±
ANGLES	±1°

MATERIAL -

FINISH -

Customer Drawing

SCALE 4:1

SHEET 1 OF 1 REV CI

1470-19 (3/11)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[1-2133394-2](#)