



COMPACT PUSH GRIP WIRE CONNECTORS

TE Connectivity's (TE) next generation compact Push Grip Wire connectors are insulated splice connectors for electrical installations. These poke-in wire splice connectors provide visual termination of 22-14 AWG solid and stranded wires. The splice is color-coded for easy identification and the compact size is designed to be used in tight spaces.

BENEFITS

- Save installation time with poke-in wire technology and tool-free conductor termination
- Easy factory or field installation with test slot for voltage testing
- Compact size with color-coded for easy identification
- Transparent housing to visually verify proper conductor insertion

APPLICATIONS

- Residential and Commercial Wiring Systems
- Retrofit Lighting
- Digital Signage
- Commercial Building Equipment
- Office Lighting

Compact Push Grip Wire Connectors

ELECTRICAL

- **Voltage:** 600 VAC rms, 600 VDC

MECHANICAL

- **Operating Temperature:** -40° to 105° C
- 22 AWG to 14 AWG
(0.35mm² – 2.5mm²)
solid and stranded wires
(see product specifications)

MATERIALS

- Polycarbonate, flame retardant to
UL94-V0 working temperature 110° C (IEC),
105° C / 221° F (UL)

SPECIFICATIONS

- **Product Specification:** [108-133070](#)
- **Application Specification:** [114-133071](#)
- **Instruction Sheet:** [408-133072](#)
- CSA 22.2 No 188
- UL486C and UL746C

PRODUCT INFORMATION

Description	Position	Color	Part Number
Push Grip Connector	2	Yellow	2324697-2
Push Grip Connector	3	Orange	2324697-3
Push Grip Connector	4	Clear	2324697-4
Push Grip Connector	5	Blue	2324697-5
Push Grip Connector	6	Purple	2324697-6



2324697-2



2324697-3



2324697-4



2324697-5



2324697-6

te.com

TE Connectivity, TE Connectivity (logo) and Every Connection Counts are trademarks. All other logos, products and/or company names referred to herein might be trademarks of their respective owners.

While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this catalog are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.

© 2018 TE Connectivity. All Rights Reserved.

1-1773964-1 10/2018 JN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[2324697-6](#)